



## SSMC Plug to SSMC Jack Right Angle Bulkhead Cable 48 Inch Length Using RG178 Coax

### RF Cable Assemblies Technical Data Sheet

PE3C4459-48

#### Configuration

- Connector 1: SSMC Plug
- Connector 2: SSMC Jack Right Angle Bulkhead
- Cable Type: RG178

#### Features

- SSMC Cable Assembly Max. Operating Frequency of 3 GHz
- Small SSMC cable connection form factor (50% smaller than SMA, radially)
- Reliable threaded coupling
- In stock and ready to ship

#### Applications

- SSMC Cable General Purpose Test
- Data Acquisition Systems
- A/D Conversion Systems
- Ultra Wideband Digital Receivers
- Software defined radio (SDR)

#### Description

Pasternack's SSMC cable assemblies are part of our full line of RF components available for same-day shipping. These SSMC cable assemblies are designed to connect SSMC system components and test connections, delivering signal frequencies as high as 12.4 GHz. Our family of SSMC cables can also be used to connect SSMC ports on data acquisition systems, A/D modules or SSMC coax patch panels. If none of our standard options fit your application, you can specify your own custom SSMC cable assembly using Pasternack's online Cable Creator.

Our SSMC cable assembly datasheet specifications and drawing with dimensions are shown below in this PDF. Pasternack's broad catalog of RF, microwave and millimeter wave cable assemblies allow designers to configure and customize their signal connections however they like. Whether the need is to provide SSMC cabling for a data acquisition system, or simply create a custom cable assembly configuration, Pasternack has the right cable assemblies for the job. Pasternack can also expertly build your custom cable assemblies for you and ship same day.

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		3	GHz
VSWR			1.5:1	
Velocity of Propagation	70			%
Capacitance	29.4 [96.46]			pF/ft [pF/m]
Operating Voltage (AC)			250	Vrms

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SSMC Plug to SSMC Jack Right Angle Bulkhead Cable 48 Inch Length Using RG178 Coax PE3C4459-48](#)


**SSMC Plug to SSMC Jack Right Angle Bulkhead  
Cable 48 Inch Length Using RG178 Coax**
**RF Cable Assemblies Technical Data Sheet**
**PE3C4459-48**
**Specifications by Frequency**

Description	F1	F2	F3	F4	F5	Units
Frequency	0.1	0.4	1	3		GHz
Insertion Loss (Typ.)	0.76	1.32	1.98	3.34		dB

**Mechanical Specifications**
**Cable Assembly**

Length\*  
Diameter

48 in [121.92 cm]  
0.156 in [3.96 mm]

**Cable**

Cable Type  
Impedance  
Inner Conductor Type  
Inner Conductor Material and Plating  
Dielectric Type  
Number of Shields  
Shield Layer 1  
Jacket Material  
Jacket Diameter

RG178  
50 Ohms  
Stranded  
Copper Clad Steel, Silver  
PTFE  
1  
Silver Plated Copper Braid  
FEP, Tan  
0.072 in [1.83 mm]

Repeated Minimum Bend Radius

0.4 in [10.16 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SSMC Plug to SSMC Jack Right Angle Bulkhead Cable 48 Inch Length Using RG178 Coax PE3C4459-48](#)



## SSMC Plug to SSMC Jack Right Angle Bulkhead Cable 48 Inch Length Using RG178 Coax

### RF Cable Assemblies Technical Data Sheet

PE3C4459-48

#### Connectors

Description	Connector 1	Connector 2
Type	SSMC Plug	SSMC Jack Right Angle Bulkhead
Impedance	50 Ohms	50 Ohms
Mating Cycles	500	500
Contact Material and Plating	Beryllium Copper, Gold	Beryllium Copper, Gold
Contact Plating Specification	MIL-G-45204	MIL-G-45204
Dielectric Type	Teflon	Teflon
Outer Conductor Material and Plating		Beryllium Copper, Gold
Outer Conductor Plating Specification		MIL-G-45204
Body Material and Plating	Beryllium Copper, Gold	Brass, Gold
Body Plating Specification	MIL-G-45204	MIL-G-45204
Coupling Nut Material and Plating	Beryllium Copper, Gold	
Coupling Nut Plating Specification	MIL-G-45205	
Torque	1.75 in-lbs [0.2 Nm]	1.75 in-lbs [0.2 Nm]

#### Mechanical Specification Notes:

\*All cable assemblies have a length tolerance of 1.5% or  $\pm 3/8"$ , whichever is greater.

#### Environmental Specifications

##### Temperature

Operating Range

-55 to +165 deg C

#### Compliance Certifications (see [product page](#) for current document)

#### Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SSMC Plug to SSMC Jack Right Angle Bulkhead Cable 48 Inch Length Using RG178 Coax PE3C4459-48](#)



## SSMC Plug to SSMC Jack Right Angle Bulkhead Cable 48 Inch Length Using RG178 Coax

### RF Cable Assemblies Technical Data Sheet

PE3C4459-48

#### How to Order

Part Number Configuration:

**PE3C4459**

- **xx**

**uu**

Unit of Measure:  
cm = Centimeters  
<blank> = Inches  
Length  
Base Number

Example: PE3C4459-12 = 12 inches long cable  
PE3C4459-100cm = 100 cm long cable

SSMC Plug to SSMC Jack Right Angle Bulkhead Cable 48 Inch Length Using RG178 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SSMC Plug to SSMC Jack Right Angle Bulkhead Cable 48 Inch Length Using RG178 Coax PE3C4459-48](#)

URL: <https://www.pasternack.com/ssmc-plug-ssmc-jack-rg178bu-cable-assembly-pe3c4459-48-p.aspx>


The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

# PE3C4459-48 CAD Drawing

SSMC Plug to SSMC Jack Right Angle Bulkhead Cable 48 Inch Length Using RG178 Coax



**SSMC R.A. JACK BULKHEAD MOUNT CONNECTOR**



**MOUNTING HOLE**

NOTES:  
 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  
 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  
 3. DIMENSIONS ARE IN INCHES [mm].

DWG TITLE	CAGE CODE	CAD FILE	SCALE	SIZE	REV
PE3C4459	53919	082217	N/A	A	9999

<b>PASTERNACK</b> THE ENGINEER'S RESOURCE	Pasternack Enterprises, Inc. P.O. Box 16759   Irvine   CA   92623	Phone: (949) 261-1920   Fax: (949) 261-7451	Website: <a href="http://www.pasternack.com">www.pasternack.com</a>   E-Mail: <a href="mailto:sales@pasternack.com">sales@pasternack.com</a>
--	--	---	--

**STANDARD TOLERANCES**  
 X  $\pm 0.2$   
 XX  $\pm 0.01$   
 XXX  $\pm 0.005$

ONLY TO DIMENSIONS IN INCHES