

Special

*Image for illustrative purpose only*

Summary

[Request a quote](#)[thermocouple](#)

Nb of contacts Thermocouple	2
Wire Size/AWG	28 - 20
Socket / Receptacle	Socket / Receptacle - Fixed Panel Front Mounted
Locking system	Push-pull
Panel Drill Hole	M16
Size	1E
Suggested matching part	FFA.1E.302.CLKC50
Series	E - Outdoor Stepped Insert

Technical details

Electrical Configuration

Nb of contacts Thermocouple	2
Contact Termination Thermocouple	Solder
Insert configuration value	1E.302/ThC - 1 Thermocouple Pair
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	15 A
ThC. Materials (P+/N-)	Chromel / Alumel
Contact Dia.	1.3 mm (0.051 in)
Wire Size/AWG	28 - 20

Form & Material



Shell style / Model id	ERA - Fixed receptacle, nut fixing
Socket / Receptacle	Fixed Panel Front Mounted
Housing material	Brass (chrome plated [SAE AMS 2460]) shell, collet nut and latch sleeve, nickel plated [SAE AMS QQ N 290] brass mid pieces
Locking system	Push-pull
Keying	Hermaphroditic keying (half moon insert) with female pin 1
Colour	Grey
Weight	18.9 g
Panel Drill Hole	M16

Environment

Technical domain	Energy and Industrial, Test and Measurement
Environmental sealing (IP rating)	IP68
Endurance	5000 mating cycles
Temperature range	-55°C / +200°C (max. temperature valid for short periods of use.)
Climatic Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	95 dB (10 MHz)
Shielding (min)	80 dB (1 GHz)
Shock Resistance	100 g [6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Drawings



Contact 1: Alumel (-)
Contact 2: Chromel (+)

Dimensions

	A	B	e	E	L	M	S1	S3	L1
mm.	20	21.5	M16x1.0	9	24	4.5	14.5	19	25.3
in.	0.79	0.85		0.35	0.94	0.18	0.57	0.75	1

Recommended By Lemo

Caps

Compatible cap	BRE.1K.200.NAS
Cap 2	BRE.1K.200.CAS

LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.