

*Image for illustrative purpose only*

## Summary

[Request a quote](#)[Catalog](#)

Nb of contacts Coax	1
Plug	Plug - Straight
Locking system	Threaded
Size	3
Suggested matching part	<a href="#">HVP.03.250.CLLP</a>

# Technical details

## Electrical Configuration

Nb of contacts Coax	1
Contact Termination Coax - Conductor fixing	Crimp
Insert configuration value	3.25 - 1 Coax (50 Ohm)
Rated current	4 A
Impedance	50 Ohms

## Form & Material

Shell style / Model id	FVS - Straight plug (coaxial) for cable crimping
Plug	Straight
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Threaded
Keying	3 keys (alpha=42, gamma=30, plug: male contacts, receptacle: female contacts)
Weight	8.25 g

## Environment

Environmental sealing (IP rating)	IP68
Temperature range	-20°C / +200°C (max. temperature valid for short periods of use.)
Climatic Category	20/200/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	100 dB (10 MHz)
Shielding (min)	80 dB (1 GHz)
Pressure	60 bars (120 bars with LEMO cable assembly)
Salt Spray Corrosion	>1000 hr


## Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Crimp

[https://www.lemo.com/int\\_en/fvs-03-250-clce31.html](https://www.lemo.com/int_en/fvs-03-250-clce31.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Drawings



## Dimensions

	<b>A</b>	<b>L</b>	<b>M</b>	<b>S1</b>	<b>S2</b>
mm.	11.8	35.3	26.5	11	5.5
in.	0.46	1.39	1.04	0.43	0.22