

Special



Image for illustrative purpose only

Summary

[Request a quote](#)

[M series](#)

[Application leaflet Security Defence](#)

Number of contacts Low Voltage	3
Gender	Standard
Socket / Receptacle	Socket / Receptacle - Fixed Panel Rear Mounted
Locking system	Ratchet
Panel Drill Hole	M13
Size	0M
Series	M - Rugged Ratchet coupling

Technical details

Electrical Configuration

Number of contacts Low Voltage	3
Contact Termination Low voltage	PCB - Straight
R (max) - electrical contact resistance	4.8 mOhm
Insert configuration value	0M.303 - 3 Low Voltage
Footprint IPC Class3 compatibility	Contact LEMO for details
Insulator	L: PEEK
Rated current	8 A
Test voltage contact-contact	1.8 kV DC
Test voltage contact-shell	1.4 kV DC
Contact Dia.	0.9 mm (0.035 in)
Gender	Standard



Form & Material

Shell style / Model id	HE - Fixed receptacle, nut fixing for printed circuit, watertight
Socket / Receptacle	Fixed Panel Rear Mounted
Housing material	Aluminium (NiCorAl Nickel fluorocarbon polymer, anthracite color) shell and nut, other pieces bronze/brass
Locking system	Ratchet
Keying	3 keys (beta=165, gamma=30, plug: male contacts, receptacle: female contacts)
Colour	Grey
Variant	Watertight unmated (connector to device)
Weight	8.47 g
Panel Drill Hole	M13

Environment

Technical domain	Motorsport, Security and Defence, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	IP68
Endurance	3000 mating cycles
Temperature range	-20°C / +80°C
EMI Shielding EIA 364-66A	≥ 80 dB (1 GHz), ≥ 70 dB (3 GHz), ≥ 58 dB (6 GHz), ≥ 40 dB (10 GHz)
Gunfire vibration	25 Hz - 2000 Hz, 3 axis (Apache helicopter)
Humidity (max)	21 days at 95%
Lighting strike EIA 364-76	10K amps - 6 times
Shock Resistance	300 g [3 ms]
Vibration-Random	37.8 g rms - 3 axes, 4 hr amb [50 Hz - 2000 Hz]
Vibration-Sine	30 g, 3 axes, 12 hr [10 Hz - 2000 Hz]
Salt Spray Corrosion	max. 500 hr

Drawings



Dimensions

	A	C	e	E	H	Ls	Lr	N	P	R	S1	S2
mm.	17	16.8	M13x0.75	5	5.08	20.8	21	16.8	5.3	13.8	11.5	14
in.	0.67	0.66		0.2	0.2	0.82	0.83	0.66	0.21	0.54	0.45	0.55

Recommended By Lemo

Tools												
Spanner 2						DCM.65.140.AZ						
Spanner wrench						DCM.65.140.AZ						

LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.