



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

[Catalog](#)

[Customer Drawing](#)

Number of contacts Low Voltage	30
Gender	Standard
Socket / Receptacle	Socket / Receptacle - Fixed Panel Rear Mounted
Locking system	Push-pull
Size	3F
Series	F - Rugged Push-Pull

# Technical details

## Electrical Configuration

Number of contacts Low Voltage	30
Contact Termination Low voltage	PCB - Straight
R (max)	6.1 mOhm
Insert configuration value	3F.330 - 30 Low Voltage
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	3.5 A
Vtest (contact-contact)	1350 V (AC), 1910 V (DC)
Vtest (contact-shell)	1200 V (AC), 1700 V (DC)
Contact Dia.	0.7 mm (0.028in)
Gender	Standard

## Form & Material

Shell style / Model id	HE - Fixed receptacle, nut fixing, for printed circuit (back panel mounting)
Socket / Receptacle	Fixed Panel Rear Mounted
Housing material	Aluminium (nickel plated [SAE AMS QQ N 290], anthracite color) shell and nut, other pieces bronze/brass
Locking system	Push-pull
Keying	3 keys (beta=150, gamma=60, plug: male contacts, receptacle: female contacts)
Colour	Grey
Variant	Watertight unmated (connector to device)
Weight	11.24 g

[https://www.lemo.com/int\\_en/solutions/optima/f-rugged-push-pull/hen-3f-330-xlnps.html](https://www.lemo.com/int_en/solutions/optima/f-rugged-push-pull/hen-3f-330-xlnps.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Environment

---

Technical domain	Motorsport, Security and Defence
Environmental sealing (IP rating)	IP68
Endurance	1000 mating cycles
Temperature range	-15°C / +100°C
Climatic Category	15/200/21 (Aluminium shell)
Humidity (max)	<=95% [at 60 deg C /140 F]
Shock Resistance	100 g [ 6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Pressure	5 bars
Salt Spray Corrosion	max. 48 hr

## Recommended By Lemo

### Accessories

---

Compatible cap	<a href="#">BRE.3F.200.XAV</a>
----------------	--------------------------------

### Tools

---

Spanner 2	<a href="#">DCM.65.190.AZ</a>
-----------	-------------------------------

Spanner wrench	<a href="#">Socket for torque wrench DCM.65.200.AZ</a>
----------------	--

## CAD

### Documents

---

PCB	<a href="#">Download</a>
-----	--------------------------

PCB Eagle	<a href="#">Download</a>
-----------	--------------------------

Kicad	<a href="#">Download</a>
-------	--------------------------

PCB Altium	<a href="#">Download</a>
------------	--------------------------

[https://www.lemo.com/int\\_en/solutions/optima/f-rugged-push-pull/hen-3f-330-xlnps.html](https://www.lemo.com/int_en/solutions/optima/f-rugged-push-pull/hen-3f-330-xlnps.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.