

Standard



Image for illustrative purpose only

Summary

[Request a quote](#)

[M series](#)

[Application leaflet Security Defence](#)

Number of contacts Low Voltage	5
Gender	Standard
Socket / Receptacle	Socket / Receptacle - Fixed Panel Rear Mounted
Locking system	Ratchet
Panel Drill Hole	M13
Size	0M
Suggested matching part	FMP.0M.305.XLC
Series	M - Rugged Ratchet coupling

https://www.lemo.com/int_en/solutions/optima/m-ratchet-coupling/hep-0m-305-xlnp.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Number of contacts Low Voltage	5
Contact Termination Low voltage	PCB - Straight
R (max) - electrical contact resistance	6.1 mOhm
Insert configuration value	0M.305 - 5 Low Voltage
Footprint IPC Class3 compatibility	Yes
Class3 Productibility Level Compatibility	B (Moderate Design Producibility - Standard)
Insulator	L: PEEK
Rated current	6.5 A
Test voltage contact-contact	1.75 kV DC
Test voltage contact-shell	1.4 kV DC
Contact Dia.	0.7 mm (0.028 in)
Gender	Standard

Form & Material

Shell style / Model id	HE - Fixed receptacle, nut fixing for printed circuit, watertight
Socket / Receptacle	Fixed Panel Rear Mounted
Housing material	Aluminium (nickel plated [SAE AMS QQ N 290], anthracite color) shell and nut, other pieces bronze/brass
Locking system	Ratchet
Keying	P: 3 keys (beta=150, gamma=60, plug: male contacts, receptacle: female contacts)
Colour	Grey
Variant	Watertight unmated (connector to device)
Weight	7.99 g
Panel Drill Hole	M13



https://www.lemo.com/int_en/solutions/optima/m-ratchet-coupling/hep-0m-305-xlnp.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Environment

Technical domain	Motorsport, Security and Defence, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	IP68
Endurance	3000 mating cycles
Temperature range	-20°C / +80°C
EMI Shielding EIA 364-66A	≥ 80 dB (1 GHz), ≥ 70 dB (3 GHz), ≥ 58 dB (6 GHz), ≥ 40 dB (10 GHz)
Gunfire vibration	25 Hz - 2000 Hz, 3 axis (Apache helicopter)
Humidity (max)	21 days at 95%
Lighting strike EIA 364-76	10K amps - 6 times
Shock Resistance	300 g [3 ms]
Vibration-Random	37.8 g rms - 3 axes, 4 hr amb [50 Hz - 2000 Hz]
Vibration-Sine	30 g, 3 axes, 12 hr [10 Hz - 2000 Hz]
Salt Spray Corrosion	max. 48 hr

Drawings



https://www.lemo.com/int_en/solutions/optima/m-ratchet-coupling/hep-0m-305-xlnp.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Dimensions

	A	C	e	E	H	Ls	Lr	N	P	R	S1	S2
mm.	17	16.8	M13x0.75	5	5.08	20.8	21	16.8	5.3	13.8	11.5	14
in.	0.67	0.66		0.2	0.2	0.82	0.83	0.66	0.21	0.54	0.45	0.55

Recommended By Lemo

Caps

Compatible cap	BGK.0M.200.XAZ
Cap 2	BMK.0M.200.XAZ

Tools

Spanner 2	DCM.65.140.AZ
Spanner wrench	DCM.65.140.AZ