

Special



Image for illustrative purpose only

Summary

[Request a quote](#)

[M series](#)

[Application leaflet Security Defence](#)

[Customer Drawing](#)

Number of contacts Low Voltage	68
Gender	Standard
Socket / Receptacle	Socket / Receptacle - Fixed Panel Rear Mounted
Locking system	Ratchet
Panel Drill Hole	M28
Size	LM
Suggested matching part	FGW.LM.368.CLCM
Series	M - Rugged Ratchet coupling

https://www.lemo.com/int_en/solutions/optima/m-ratchet-coupling/hew-lm-368-clnp.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Number of contacts Low Voltage	68
Contact Termination Low voltage	PCB - Straight
R (max)	6.1 mOhm
Insert configuration value	LM.368 - 68 (0.7 mm) Low Voltage
Footprint IPC Class3 compatibility	Yes
Class3 Productibility Level Compatibility	A (General Design Producibility - Preferred)
Insulator	L: PEEK
Rated current	2.5 A
Test voltage contact-contact	1.96 kV DC
Test voltage contact-shell	2.3 kV DC
Contact Dia.	0.7 mm (0.028in)
Gender	Standard

Form & Material

Shell style / Model id	HE - Fixed receptacle, nut fixing for printed circuit, watertight
Socket / Receptacle	Fixed Panel Rear Mounted
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Ratchet
Keying	W: 5 keys (alpha=95, beta=115, gamma=35, delta=25, plug: male contacts, receptacle: female contacts)
Colour	Grey
Variant	Watertight unmated (connector to device)
Weight	29.32 g
Panel Drill Hole	M28

https://www.lemo.com/int_en/solutions/optima/m-ratchet-coupling/hew-lm-368-clnp.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Environment

Technical domain	Motorsport, Security and Defence, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	IP68
Endurance	3000 mating cycles
Temperature range	-20°C / +80°C
EMI Shielding EIA 364-66A	>= 80 dB (1 GHz), >=70 dB (3 GHz), >= 58 dB (6 GHz), >= 40 dB (10 GHz)
Gunfire vibration	25 Hz - 2000 Hz, 3 axis (Apache helicopter)
Humidity (max)	21 days at 95%
Lighting strike EIA 364-76	10K amps - 6 times
Shock Resistance	300 g [3 ms]
Vibration-Random	37.8 g rms - 3 axes, 4 hr amb [50 Hz - 2000 Hz]
Vibration-Sine	30 g, 3 axes, 12 hr [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

Recommended By Lemo

Caps

Compatible cap	BGK.LM.200.XAZ
Cap 2	BMK.LM.200.XAZ

Tools

Spanner 2	DCM.65.290.AZ
Spanner wrench	DCM.65.290.AZ

CAD

Documents

PCB Eagle	Download
-----------	--------------------------

https://www.lemo.com/int_en/solutions/optima/m-ratchet-coupling/hew-lm-368-clnp.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.