

Standard



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

[P series catalog](#)

[Industry Brochure Medical](#)

[Customer Drawing](#)

|                                    |                               |
|------------------------------------|-------------------------------|
| Number of contacts Low Voltage     | 5                             |
| Wire Size/AWG                      | 30 - 22                       |
| Gender                             | Standard                      |
| Plug                               | Plug - Straight               |
| Locking system                     | Push-pull                     |
| Jacket cable outside diameter [mm] | 5.30 - 6.50 mm                |
| Size                               | 1P                            |
| Suggested matching part            | <a href="#">PLA.M0.5GL.LJ</a> |
| Series                             | REDEL P - Push-Pull           |

[https://www.lemo.com/int\\_en/solutions/redel/redel-p-push-pull/paa-m0-5gl-ac65j.html](https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/paa-m0-5gl-ac65j.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

|                                         |                               |
|-----------------------------------------|-------------------------------|
| Number of contacts Low Voltage          | 5                             |
| Contact Termination Low voltage         | Solder                        |
| R (max) - electrical contact resistance | 4.5 mOhm                      |
| Insert configuration value              | 1P.M05 - 5 Low Voltage        |
| Insulator                               | L: PEEK (UL 94 / V-0/1.5)     |
| Rated current                           | 7 A                           |
| Test voltage contact-contact            | 1.48 (kV DC)                  |
| Max. Solid Conductor                    | 0.34 mm <sup>2</sup> (AWG 22) |
| Max. Stranded Conductor                 | 0.34 mm <sup>2</sup> (AWG 22) |
| Air clearance                           | 0.8 mm                        |
| Creepage distance                       | 0.8 mm                        |
| Bucket Dia.                             | 0.8 mm (0.031 in)             |
| Contact Dia.                            | 0.9 mm (0.035 in)             |
| Wire Size/AWG                           | 30 - 22                       |
| Gender                                  | Standard                      |

## Form & Material

|                        |                                                                        |
|------------------------|------------------------------------------------------------------------|
| Shell style / Model id | PA - Straight plug with cable collet                                   |
| Plug                   | Straight                                                               |
| Housing material       | PSU (Polysulfone), grey                                                |
| Locking system         | Push-pull                                                              |
| Keying                 | A: 2 keys (alpha=40, Plug: male contacts, Receptacle: female contacts) |
| Colour                 | Grey - Yellow                                                          |
| Variant                | Yellow collet nut                                                      |
| Weight                 | 5.18 g                                                                 |

[https://www.lemo.com/int\\_en/solutions/redel/redel-p-push-pull/paa-m0-5gl-ac65j.html](https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/paa-m0-5gl-ac65j.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Environment

|                                   |                                                                                                                                                                                                                                |
|-----------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Technical domain                  | Energy and Industrial, Medical, Test and Measurement, Transportation, Aerospace and UAV                                                                                                                                        |
| Environmental sealing (IP rating) | IP50                                                                                                                                                                                                                           |
| Endurance                         | > 5000 mating cycles                                                                                                                                                                                                           |
| Temperature range                 | -50°C / +150°C                                                                                                                                                                                                                 |
| F ret (max)                       | 150 N                                                                                                                                                                                                                          |
| F ret (min)                       | 50 N                                                                                                                                                                                                                           |
| Steam sterilization               | Compiles with ISO 17665:2024 sterilization standard for autoclave, ISO 11135:2014 for EtO, and ISO 11137-1, -2, -3 standards for gamma, e-beam x-ray. For more details on sterilization methods and cycles, please contact us. |

Cable fixation

|                                    |                                              |
|------------------------------------|----------------------------------------------|
| Cable termination protection       | Standard back nut (no additional protection) |
| Fixation type                      | Cable collet                                 |
| Jacket cable outside diameter [mm] | 5.30 - 6.50 mm                               |

Cables

| Cable PartNumber | Material | Colour | Cable image                                                                           |
|------------------|----------|--------|---------------------------------------------------------------------------------------|
| 150250           | PVC      | Grey   |  |