



Image for illustrative purpose only

Summary

[Request a quote](#)

[P series catalog](#)

[Customer Drawing](#)

Number of contacts Low Voltage	5
Wire Size/AWG	30 - 22
Gender	Standard
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	4.00 - 5.20 mm
Size	1P
Suggested matching part	PLB.M0.5GL.LG PKB.M0.5GL.NG
Series	REDEL P - Push-Pull

https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/pab-m0-5gl-ac52g.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Number of contacts Low Voltage	5
Contact Termination Low voltage	Solder
R (max)	4.5 mOhm
Insert configuration value	1P.M05 - 5 Low Voltage
Footprint IPC Class3 compatibility	No
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	7 A
Test voltage contact-contact	1.48 (kV DC)
Max. Solid Conductor	0.34 mm ² (AWG 22)
Max. Stranded Conductor	0.34 mm ² (AWG 22)
Air clearance	0.8 mm
Creepage distance	0.8 mm
Bucket Dia.	0.8 mm (0.031in)
Contact Dia.	0.9 mm (0.035in)
Wire Size/AWG	30 - 22
Gender	Standard

Form & Material

Shell style / Model id	PA - Straight plug with cable collet
Plug	Straight
Housing material	PSU (Polysulfone), grey
Locking system	Push-pull
Keying	B: 2 keys (alpha=60, Plug: male contacts, Receptacle: female contacts)
Colour	Grey
Variant	Grey collet nut
Weight	5.21 g

https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/pab-m0-5gl-ac52g.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Environment

Technical domain	Energy and Industrial, Medical, Test and Measurement, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	IP50
Endurance	> 5000 mating cycles
Temperature range	-50°C / +150°C
F ret (max)	150 N
F ret (min)	50 N
Steam sterilization	Compiles with ISO 17665:2024 sterilization standard for autoclave, ISO 11135:2014 for EtO, and ISO 11137-1, -2, -3 standards for gamma, e-beam x-ray. For more details on sterilization methods and cycles, please contact us.

Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	4.00 - 5.20 mm

CAD

Documents

Eplan	Download
-------	--------------------------

Cables

Cable PartNumber	Material	Colour	Cable image
CMN.05.T22.051QGZE	TPR (medical)	Grey	
50090	PVC	Black	
50140	PVC	Grey	