


**PolarTEC™ PT Series Thermoelectric Cooler**


The PT4-12-F2-3030-TA-W6 is a porch-style thermoelectric cooler. The hot side ceramic has an extended edge, which allows for a strong lead attachment to accommodate the wiring of multiple thermoelectric coolers into an array. It has a maximum  $Q_c$  of 33 Watts when  $\Delta T = 0$  and a maximum  $\Delta T$  of 70.5 °C at  $Q_c = 0$ .

**Features**

- Strong lead attachment
- Precise temperature control
- Reliable solid-state operation
- No sound or vibration
- DC Operation
- RoHS-compliant

**Applications**

- Cooling for Mobile Base Stations and Cell Towers
- Thermal Management Solutions for Beverage Cooling
- Cooling for Centrifuges
- Energy Storage Systems





CERAMIC MATERIAL:  $\text{Al}_2\text{O}_3$   
SOLDER CONSTRUCTION: 138°C, BiSn


INCHES [ MM ]

## Electrical and Thermal Performance


For maximum performance, be sure to orient the CONTROL side of the TEC against the application to be managed and the AMBIENT side against the heat sink or other heat rejection method. The CONTROL side is always opposite the side with lead attachments. Lead attachment is a passive heat loss and less impactful if located on the side that attaches to the heat exchanger.




Current vs Voltage (I vs V)  
 $Thot = 27^\circ\text{C}$




Coefficient of Performance (COP =  $Q_c/P_{in}$ )  
 $Thot = 27^\circ C$




Coefficient of Performance (COP =  $Q_c/P_{in}$ )  
 $Thot = 27^\circ C$




Total Heat Dissipated at Hot Side ( $Q_h = Q_c + P_{in}$ )  
 $Thot = 27^\circ C$




Total Heat Dissipated at Hot Side ( $Q_h = Q_c + P_{in}$ )  
 $Thot = 27^\circ C$



Heat Pumped at Cold Side ( $Q_c$ )  
 $Thot = 35^\circ C$  |  $I_{operating} = 3.4$  Amps



Coefficient of Performance (COP =  $Q_c/P_{in}$ )  
 $Thot = 35^\circ C$  |  $I_{operating} = 3.4$  Amps



## Specifications

Hot Side Temperature	27.0 °C	35.0 °C	50.0 °C
Qcmax ( $\Delta T = 0$ )	33.0 Watts	34.0 Watts	35.8 Watts
$\Delta T_{max}$ ( $Q_c = 0$ )	70.5°C	73.5°C	78.8°C
I <sub>max</sub> (I @ $\Delta T_{max}$ )	4.0 Amps	4.0 Amps	3.9 Amps
V <sub>max</sub> (V @ $\Delta T_{max}$ )	13.9 Volts	14.4 Volts	15.4 Volts
Module Resistance	3.24 Ohms	3.37 Ohms	3.62 Ohms
Max Operating Temperature	80 °C		
Weight	11.0 gram(s)		

## Finishing Options

Suffix	Thickness	Flatness / Parallelism	Hot Face	Cold Face	Lead Length
TA	3.200 ±0.025 mm 0.126 ± 0.0010 in	0.025 mm / 0.025 mm 0.001 in / 0.001 in	Lapped	Lapped	152.4 mm 6.00 in

## Sealing Options

Suffix	Sealant	Color	Temp Range	Description
	None			No sealing specified

## Notes

Max operating temperature: 80°C  
Do not exceed I<sub>max</sub> or V<sub>max</sub> when operating module  
Reference assembly guidelines for recommended installation

Any information furnished by Tark Thermal Solutions and its agents, whether in specifications, data sheets, product catalogues or otherwise, is believed to be (but is not warranted as being) accurate and reliable, is provided for information only and does not form part of any contract with Tark Thermal Solutions. All specifications are subject to change without notice. Tark Thermal Solutions assumes no responsibility and disclaims all liability for losses or damages resulting from use of or reliance on this information. All Tark products are sold subject to the Tark Thermal Solutions Terms and Conditions of sale (including Tark's limited warranty) in effect from time to time, a copy of which will be furnished upon request.

© Copyright 2025 Tark Thermal Solutions, Inc. All rights reserved.

PolarTEC™ is a trademark of Tark Thermal Solutions, Inc. All other marks are owned by their respective owners.

Revision: 00 Date: 06-01-2022

Print Date: 05-29-2025