

# Data sheet

## OpDAT REGplus 4xSC/ST-Duplex MM for shrink splice holder


Page 1/5

P/N  
150240C30410S  
EAN 4250184152576  
2025/09/17  
Version: AC

### Illustrations



Dimensional drawing



See enlarged drawings at the end of document

### Product specification

- splice distributor for TH35 rail
- equipped with SC-D/ST-D (MM) adapters made of zinc die-casting
- slotted ceramic sleeve for multi mode applications
- with fiber reservoir
- custom-labeled identification strips
- various mounting versions on rail
- splice tray with shrink splice holder
- front plate can be completely removed
- cable feed from top or bottom, straight or inclined, with M20 cable gland (up to 2 possible)
- feed of preassembled cables is possible
- one cable gland M20 with strain relief included in the delivery
- housing cover fastening by means of just one captive screw
- unoccupied adapter recesses are closed with special blind plugs
- variants: equipped with 2, 3, 4 or 6 SC-D/ST-D adapters (SC-D interior, ST-D exterior)
- please note: if you use preassembled cables with ST plugs, use the unequipped version of the OpDAT REG plus. The ST-D adapters required in this case are available as accessory. Before mounting the adapters in the housing, plug the preassembled ST plugs in the adapters for reasons of space.



# OpDAT REGplus 4xSC/ST-Duplex MM for shrink splice holder

P/N  
150240C30410S  
EAN 4250184152576  
2025/09/17  
Version: AC

## Technical Data

### General Data

Fields of application	structured building cabling office areas data center
Mechanical measurement according to MICE	M1
Ingress measurement according to MICE	I1
Climatic measurement according to MICE	C1
Electromagnetic measurement according to MICE	E3
Design	Splice distributor
Mounting style	Standard rail TH35
Transmission technology	Fiber optic
Color	metallike
Dimensions	
Dimension (L x W x H)	144.8 mm x 143.8 mm x 34 mm
Dimension (L x W x H)	5.701 in. x 5.661 in. x 1.339 in.
Mode type of the fiber	Multimode
Labeling option	label strip / labeling strip

### Connections/interfaces

Connector technology interface 1	SC-D/ST-D Couplers
Connector technology interface 2	SC-D/ST-D Couplers
Number of ports interface 1	6
Number of ports interface 2	6
Number of equipped ports interface 1	4
Number of ports interface 2 equipped	4
Number of ports with dust protection interface 1	4
Number of ports with dust protection interface 2	4
Number of blind	2
Cable access/outlet	from top or bottom, straight or inclined

### Mechanical data

Cut-out	SC-D, LC-Q, ST-D
Connector type	duplex
Life - Number of mating cycles	min. 500
strain relief	M gland

Data sheet

Page 3/5

# OpDAT REGplus 4xSC/ST-Duplex MM for shrink splice holder

P/N

150240C30410S

EAN 4250184152576

2025/09/17

Version: AC

## Technical Data

### Materials and material properties

Material - Housing	sheet steel
Material - Sleeve	ceramic, slotted
Material - Coupler housing	GD-Zn
Halogen free	yes
RoHS	compliant

### Classifications

ETIM 7.0	EC001130
ETIM 8.0	EC001130
ETIM 9.0	EC001130
ETIM 10.0	EC001130

### Packing details

Type of packaging	1 pc(s) / box
-------------------	---------------

### Application note

This product is a standard product of METZ CONNECT. METZ CONNECT is not aware of the specific intended use of the goods by the Customer or any customers of the Customer. The Customer guarantees that it has fully and sufficiently tested the use of the goods and any product modifications, product changes or product enhancements with regard to the specific intended use in accordance with the state of the art or in any other way. At METZ CONNECT's request, the Customer shall submit and make available meaningful evidence (e.g. test and laboratory protocols, certifications, etc.).



Data sheet

Page 4/5

## OpDAT REGplus 4xSC/ST-Duplex MM for shrink splice holder

P/N

150240C30410S

EAN 4250184152576

2025/09/17

Version: AC

### Accessories

P/N	Designation
899789-01	Label sheet for E-DAT C6 and E-DAT design patch panels



Data sheet

# OpDAT REGplus 4xSC/ST-Duplex MM for shrink splice holder

Page 5/5

P/N  
150240C30410S  
EAN 4250184152576  
2025/09/17  
Version: AC

## Illustrations

Dimensional drawing

