

4-Post 12U Mobile Open Frame Server Rack, Four Post 19" Network Rack with Wheels, Rolling Rack with Adjustable Depth for Computer/AV/Data/IT Equipment - Casters, Leveling Feet or Floor Mounting

Product ID: 4POSTRACK12U



The 4POSTRACK12U 12U Server Rack lets you store your servers, network and telecommunications equipment in a sturdy, adjustable depth open-frame rack.

Designed with ease of use in mind, this 12U rack offers easy-to-read markings for both rack units (U) and depth, with a wide range of mounting depth adjustments (22 - 40in) that make it easy to adapt the rack to fit your equipment.

This durable 4-post rack supports a static loading capacity of up to 1200lbs (544kg), and offers compliance with several industry rack standards (EIA/ECA-310, IEC 60297, DIN 40494) for a universal design that's compatible with most rack equipment.

For a complete server storage solution that saves you time and hassle, the rack includes optional accessories such as casters, leveling feet and cable management hooks. The base is also pre-drilled for securely fastening the rack to the floor if needed, providing you with additional stability to better suit your server environment.

## Certifications, Reports and Compatibility



## Applications

- Durable storage for rackmount servers, KVM switches, and networking equipment
- Suitable for rackmount equipment where security at the rack level is not required

- Rack-mounting A/V equipment in a radio or television studio

## Features

- **ADJUSTABLE DEPTH:** 4- Post 12U open frame server rack with 4 vertical rails and adjustable mounting depth 22" to 40" (56,0cm to 101,7cm); Compatible with various servers / switches / data / AV and other IT equipment; EIA/ECA-310-E Compliant
- **EASY ASSEMBLY:** Mobile network rack with easy-to-follow assembly instructions and online video; Compact flat-pack shipping to avoid damage and facilitate installation; Only 25in (64cm) high, ideal for utility/server closets or narrow home/office spaces
- **COLD ROLLED STEEL:** Durable 4 Post 19" open frame rack designed for ventilation with 12U mounting height and 1200lb (544kg) weight capacity (stationary); 3 install options included: casters, levelling feet, or base-plate to secure rack to the floor
- **HARDWARE INCLUDED:** Rolling computer/data rack includes cage nuts and screws to mount equipment, easy to read Units (U) and depth adjustment markings, cable management hooks for organization, and required assembly tools
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this 12U rack is backed for 2-years, including free lifetime 24/5 multi-lingual technical assistance

---

### Hardware

|                  |                                       |
|------------------|---------------------------------------|
| Warranty         | 2 Years                               |
| Wallmountable    | No                                    |
| Rack Type        | 4-Post                                |
| Frame Type       | Open Frame                            |
| U Height         | 12U                                   |
| Special Features | Adjustable Mounting Rails             |
|                  | Base Plate with Floor-Anchoring Holes |
|                  | Built-in Cable Management             |
|                  | Casters (Included)                    |
|                  | Easy Assembly                         |
|                  | Grounding Lug(s)                      |
|                  | Leveling Feet                         |
|                  | U-Markings                            |

---

|                       |                       |
|-----------------------|-----------------------|
| Mounting Rail Profile | L-Shape               |
| Mounting Hole Types   | Square (For Cage Nut) |
| Industry Standards    | EIA/ECA-310-E         |

---

#### Performance

|                              |                    |
|------------------------------|--------------------|
| Weight Capacity (Stationary) | 1199.5 lb [544 kg] |
|------------------------------|--------------------|

---

#### Physical Characteristics

|                       |       |
|-----------------------|-------|
| Color                 | Black |
| Construction Material | Steel |

---

#### Product Measurements

|                             |                    |
|-----------------------------|--------------------|
| Product Length              | 3.7 ft [1.1 m]     |
| Product Width               | 23.6 in [60.0 cm]  |
| Product Height              | 25.1 in [63.8 cm]  |
| Weight of Product           | 50.1 lb [22.7 kg]  |
| Maximum Mounting Depth      | 40.0 in [101.7 cm] |
| Minimum Mounting Depth      | 22.0 in [56 cm]    |
| Product Height with Casters | 28.0 in [71 cm]    |

---

#### Packaging Information

|                               |                   |
|-------------------------------|-------------------|
| Flat Pack (Assembly Required) | Yes               |
| Package Length                | 14.2 in [36.1 cm] |
| Package Width                 | 26.1 in [66.4 cm] |
| Package Height                | 6.0 in [15.3 cm]  |
| Shipping (Package) Weight     | 56.0 lb [25.4 kg] |

---

#### What's in the Box

|                     |                             |
|---------------------|-----------------------------|
| Included in Package | 2 - Left Vertical Rail      |
|                     | 2 - Right Vertical Rail     |
|                     | 2 - Base Bracket            |
|                     | 8 - Corner Section          |
|                     | 4 - Center Section          |
|                     | 2 - Top Bracket             |
|                     | 48 - M8 Bolt                |
|                     | 48 - M8 Washer              |
|                     | 1 - M8 (13mm) Wrench        |
|                     | 1 - M6 (10mm) Wrench        |
|                     | 1 - Phillips Screwdriver    |
|                     | 24 - M6 Cage Nut            |
|                     | 24 - PVC Cup Washer         |
|                     | 24 - M6 Phillips Head Screw |
|                     | 4 - Cable Management Hook   |
|                     | 4 - Hook Mounting Screw     |
|                     | 4 - Casters                 |
|                     | 4 - Leveling Feet           |
|                     | 16 - M6 Screw               |
|                     | 16 - M6 Flat Washer         |
|                     | 16 - M6 Flange Nut          |
|                     | 4 - Grounding Wires         |

---

**Warranty  
Information**

Warranty 2 Years

---

*\*Product appearance and specifications are subject to change without notice.*