

## 10 ft DVI-D Dual Link Cable - M/M

**Product ID:** DVIDDMM10



The DVIDDMM10 10ft DVI-D Dual Link cable features 2 male DVI (25-pin) connectors and provides a reliable, purely digital connection between your desktop or laptop computer and a DVI-D monitor or projector.

The 10 ft DVI-D digital monitor cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

## Certifications, Reports and Compatibility



## Applications

- Connect your desktop or laptop computer to a DVI-D Dual Link display or projector

## Features

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec
- Ferrite core eliminates EMI interference

- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices
- Compliant with DVI DDWG Standards

---

**Hardware**

Warranty	Lifetime
Connector Plating	Nickel
Cable Shield Material	Aluminum-Mylar Foil with Braid
Industry Standards	DVI DDWG Standard

---

**Connector(s)**

Connector A	1 - DVI-D (25 pin)
Connector B	1 - DVI-D (25 pin)

---

**Environmental**

Operating Temperature	0C to 50C (32F to 122F)
Storage Temperature	-20 to 70C (-4F to 158F)
Humidity	0 to 95%

---

**Physical Characteristics**

Color	Black
Wire Gauge	28 AWG
Cable Length	10.0 ft [3.0 m]
Product Length	10.0 ft [3.0 m]
Product Width	1.5 in [3.7 cm]
Product Height	0.6 in [1.6 cm]
Weight of Product	12.9 oz [366.0 g]

---

**Packaging Information**

Package Quantity	1
Package Length	13.2 in [33.5 cm]

Package Width 5.3 in [13.5 cm]

Package Height 1.7 in [4.2 cm]

Shipping (Package) Weight 13.5 oz [382.0 g]

---

**What's in the Box**

Included in Package 1 - 10 ft DVI-D Dual Link Cable - M/M

---

**Warranty  
Information**

Warranty Lifetime

---

*\*Product appearance and specifications are subject to change without notice.*

