

Gigabit Ethernet Fiber Media Converter with Open SFP Slot - TAA

Product ID: ET91000SFP2



The ET91000SFP2 Open SFP Fiber Media Converter converts and extends a Gigabit Ethernet connection over fiber, using the Gigabit SFP of your choice.

A versatile solution for connecting an Ethernet (1000Base-T) network to remote network segments over a fiber backbone, the media converter features an open SFP slot that lets you choose the MSA-Compliant Gigabit SFP that best suits your fiber connection mode (single / multi-mode) and distance requirements (see our full line of for compatible solutions).

The fiber to Ethernet converter has a durable all-steel chassis and offers simple plug-and-play installation, while support for full-duplex operation and Jumbo Frame support provides efficient network operation.

For applications where multiple chassis-mounted media converters are required, this Gigabit media converter can be purchased as a Card Module only (ET91000SFP2C).

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Cost-effective way to extend/bridge networks using fiber cabling
- Provides connectivity to a user or network segment that is in an isolated area of a large complex or in another building altogether

- Perfect for secure connections required by government agencies where EMI is not acceptable
- Connect traffic control/monitoring systems at extreme distances to the main office
- Extend network connectivity to remote areas of stadiums, auditoriums or other venues

Features

- Open SFP slot supports MSA-Compliant Single / Multi-Mode Gigabit SFPs at varying distances
- Advanced features include Link-loss forwarding, remote monitor status, two frame lengths
- Supports full or half-duplex operation
- Easy to use and install
- Jumbo Frame support

Hardware

Warranty	2 Years
PoE	No
WDM	No
Industry Standards	IEEE 802.3ab 1000BASE-T IEEE 802.3z 1000BASE-SX IEEE 802.3z 1000BASE-LX
Chipset ID	Marvell - 88E1111

Performance

Maximum Data Transfer Rate	1.25 Gbps
Type	Single Mode / Multi Mode
Fiber Operating Mode	Half/Full-Duplex
Auto MDIX	Yes
MTBF	65, 000 Hours

Connector(s)

Local Unit Connectors	1 - RJ-45
-----------------------	-----------

1 - SFP Slot

Special Notes / Requirements

Note	Fiber data transfer speeds and distances are dependent on the SFP used (sold separately)
------	--

Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.36 A
Output Voltage	12V DC
Output Current	1 A
Center Tip Polarity	Positive
Plug Type	M
Power Consumption (In Watts)	8

Environmental

Operating Temperature	0C to 60C (32F to 140F)
Storage Temperature	-10C to 70C (14F to 158F)
Humidity	10~90% RH (Non-Condensing)

Physical Characteristics

Color	Black
Material	Steel
Product Length	6.1 in [15.4 cm]
Product Width	3.5 in [8.8 cm]
Product Height	0.9 in [2.3 cm]
Weight of Product	14.0 oz [396 g]

Packaging Information

Package Quantity	1
Package Length	8.0 in [20.4 cm]
Package Width	5.4 in [13.8 cm]
Package Height	3.5 in [9.0 cm]
Shipping (Package) Weight	1.7 lb [0.8 kg]

What's in the Box

Included in Package	1 - Fiber Media Converter 1 - Universal power adapter: comes ready for NA/EU/UK only when you buy in NA/EU/UK; comes ready for Australia and New Zealand only when you buy in Australia and New Zealand 1 - Grounding Screw 1 - Instruction Manual
---------------------	---

Warranty Information

Warranty	2 Years
----------	---------

****Product appearance and specifications are subject to change without notice.***

