

Special



Image for illustrative purpose only

Summary

[Request a quote](#)

[Coax triax mixed en](#)

Nb of contacts Coax	1
Locking system	Push-pull
Panel Drill Hole	M25
Size	4S
Series	S - Indoor Stepped Insert

https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/rad-4s-250-ctm.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Nb of contacts Coax	1
Insert configuration value	4S.250 - 1 Coax (50 Ohm)
Insulator	T: PTFE
Rated current	36 A
Impedance	50 Ohms
VSWR	1.01 + 1.9 * f/GHz
Vtest	2100 V (AC), 3000 V (DC)
Cable type	RG 214 /U, RG 216 /U, RG 225 /U, RG 225 /U, RG 213/U, RG 115 A/U, RG 11 A/U, RG 144/U, RG 165 /U
Contact Dia.	4 mm (0.16in)

Form & Material

Shell style / Model id	RAD - Fixed coupler, nut fixing
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	Circular, female
Colour	Grey
Weight	87.42 g
Panel Drill Hole	M25


Environment

Technical domain	Audio Video, Energy and Industrial, Semiconductor, Test and Measurement
Environmental sealing (IP rating)	IP50
Endurance	5000 mating cycles
Temperature range	-55°C / +250°C (max. temperature valid for short periods of use.)
Climatic Category	55/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	75 dB (10 MHz)
Shielding (min)	40 dB (1 GHz)
Shock Resistance	100 g [6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/rad-4s-250-ctm.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Drawings



Dimensions

	A	B	e	E	L	M	S2
mm.	28	32	M25x1.0	12	46.5	2.5	30
in.	1.1	1.26		0.47	1.83	0.1	1.18

Recommended By Lemo

Caps

Compatible cap	BRE.4S.200.NAS
Cap 2	BRE.4S.200.NAV