

[Standard](#)

Image for illustrative purpose only

Summary

[Request a quote](#)[REDEL SP series en](#)[Industry Brochure Medical](#)[Customer Drawing](#)

Number of contacts Low Voltage	8
Wire Size/AWG	30 - 22
Gender	Standard
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	4.00 - 5.20 mm
Size	SP
Suggested matching part	SLN.M08.BLLB SRN.M08.BLL.5B
Series	REDEL SP - Inner Push-Pull

Technical details

Electrical Configuration

Number of contacts Low Voltage	8
Contact Termination Low voltage	Solder
R (max) - electrical contact resistance	4.5 mOhm
Insert configuration value	SP.M08 - 8 Low V.
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	5 A
Test voltage contact-contact	2.1 (kV DC)
Max. Solid Conductor	0.34 mm ² (AWG 22)
Max. Stranded Conductor	0.34 mm ² (AWG 22)
Air clearance	0.75 mm
Creepage distance	0.75 mm
Bucket Dia.	0.8 mm (0.031 in)
Contact Dia.	0.9 mm (0.035 in)
Wire Size/AWG	30 - 22
Gender	Standard

Form & Material

Shell style / Model id	SA - Straight plug, key (N) or keys (P, S and T), with white cable collet
Plug	Straight
Housing material	Proprietary sulfone, white
Locking system	Push-pull
Keying	3 keys (alpha=0, gamma=30, plug: male contacts, receptacle: female contacts)
Colour	White
Variant	White collet nut
Weight	47.1 g


Environment

Technical domain	Medical
Environmental sealing (IP rating)	IP50
Endurance	>5000 mating cycles
Temperature range	-50°C / +170°C
Steam sterilization	> 100 times

Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	4.00 - 5.20 mm

Cables

Cable PartNumber	Material	Colour	Cable image
CMN.08.T26.042QGZE	TPR (medical)	Grey	
108240	PTFE	White	
108260	PTFE	White	
8280	PVC	Black	

LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.