

Special



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

---

00and01Coaxial en

---

[Customer Drawing](#)

Nb of contacts Coax	1
Locking system	Push-pull
Size	00
Series	00 - NIM-CAMAC

[https://www.lemo.com/int\\_en/solutions/specialties/00-nim-camac/swh-00-250-ctmv.html](https://www.lemo.com/int_en/solutions/specialties/00-nim-camac/swh-00-250-ctmv.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Nb of contacts Coax	1
Insert configuration value	0.25 - 1 Coax (50 Ohm)
Footprint IPC Class3 compatibility	No
Insulator	T: PTFE
Rated current	4 A
Impedance	50 Ohms
VSWR	1.09 + 0.11 * f/GHz
Vtest	2100 V (AC), 3000 V (DC)
Contact retention	18 N
Contact Dia.	0.7 mm (0.03in)

## Form & Material

Shell style / Model id	SWH - Fixed coupler, nut fixing, watertight or vacuum-tight
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	Circular, female
Colour	Grey
Weight	5.04 g

## Environment

Environmental sealing (IP rating)	IP50
Endurance	5000 mating cycles
Temperature range	-20°C / +100°C
F ret (min)	100 N
Salt Spray Corrosion	>1000 hr

## Cable fixation

Panel Drill Hole	M7
------------------	----

[https://www.lemo.com/int\\_en/solutions/specialties/00-nim-camac/swh-00-250-ctmv.html](https://www.lemo.com/int_en/solutions/specialties/00-nim-camac/swh-00-250-ctmv.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Recommended By Lemo

## Accessories

---

Compatible cap

BRE.00.200.NAS

[https://www.lemo.com/int\\_en/solutions/specialties/00-nim-camac/swh-00-250-ctmv.html](https://www.lemo.com/int_en/solutions/specialties/00-nim-camac/swh-00-250-ctmv.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.