

4U 19in Steel Vertical Wall Mount Equipment Rack Bracket - TAA

Product ID: RK419WALLV



The RK419WALLV 4U Wallmount Rack Bracket offers a versatile storage solution, allowing equipment (Network devices, power strips, patch panels) to be mounted vertically (flush with the wall) to save space. Alternatively, the 4U bracket can be installed under a desk for horizontal installation, making it easy to access installed equipment directly from your workspace. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

Perfect for SoHo (small office, home office) environments, the wallmount bracket offers space-saving installation for environments lacking the footprint space for a full size server equipment rack.

Suitable for mounting on virtually any wall/ceiling surface (e.g. drywall), the bracket mounting holes (used to mount to a wall or the desk underside) are positioned at exactly 16in apart, matching standard construction framework.

Constructed to EIA-310 19in rack standards, the wallmount bracket features a sturdy steel design and is backed by StarTech.com's Lifetime Warranty.

Need more storage space? StarTech.com also offers a 1U 19in Wallmount Bracket, a 2U 19in Wallmount Bracket and a 3U 19in Wallmount Bracket.

Certifications, Reports and Compatibility



Applications

- Mount networking and telecommunication equipment flush against the wall

- Mount KVM switches or workstations under a desk or work bench to free up work space
- Ideal for small and medium businesses needing rack solutions

Features

- **4U VERTICAL WALL MOUNT RACK:** This patch panel wall mount supports 19" rack-mountable IT/AV/Network equipment of any depth; 125,0 lb [56,7 kg] Weight capacity; EIA-310 and REACH Compliant; Compact wall mount design for minimal footprint in server room/closet
- **READY TO USE:** The wall mount vertical rack ships fully assembled, and includes 6x Wood Screws, and 12x M5 Cage Nuts and Screws for mounting the rack and equipment; Two mounting holes support 16in wood stud spacing
- **BUILT TO LAST:** The vertical rack is made from solid steel for durability; Provides a solid and stable anchor to mount equipment; The powder coated paint and interior corner welding ensures long-lasting use and sturdiness
- **VERSATILE FUNCTIONALITY:** This TAA compliant multi-use low profile 4U vertical rack mount bracket enables servers, networking switches, patch panels or AV equipment to be mounted vertically for easy equipment access where a full rack is not desirable
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this vertical wall mount patch panel bracket is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	Lifetime
Wallmountable	Yes
Rack Type	2-Post
Frame Type	Open Frame
U Height	4U
Mounting Rail Profile	L-Shape
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

Performance

Weight Capacity	125.0 lb [56.7 kg]
-----------------	--------------------

Special Notes / Requirements

Note	Package includes 1" screws for mounting to wood surfaces, additional hardware will be required for other materials
------	--

Physical Characteristics

Color Black

Construction Material Steel

Product Measurements

Product Length 5.9 in [15.1 cm]

Product Width 19.8 in [50.4 cm]

Product Height 7.6 in [19.3 cm]

Weight of Product 2.4 lb [1.1 kg]

Packaging Information

Flat Pack (Assembly Required) No

Package Length 8.6 in [21.9 cm]

Package Width 21.6 in [54.9 cm]

Package Height 7.0 in [17.9 cm]

Shipping (Package) Weight 4.1 lb [1.9 kg]

What's in the Box

Included in Package 1 - Vertical Wall Mount Bracket

16 - M5 Cage Nuts

16 - M5 Screws

6 - Wood Screws

1 - Instruction Manual

Warranty Information

Warranty Lifetime

**Product appearance and specifications are subject to change without notice.*