

2-Post 6U Wall Mount Network Cabinet with Acrylic Door, 19" Wall-Mounted Server Rack for Data / AV / Electronics / Computer Equipment, Small Vented Rack Enclosure

Product ID: RK619WALL



The RK619WALL Wall Mounted 6U Server Rack/Cabinet can be fastened to most types of walls and features a sturdy, compact design that can be positioned almost anywhere without wasting valuable floor space.

This equipment rack offers 6U of storage space and is designed to accommodate 19-inch (wide) servers, networking and telecom equipment. The rack features a 12cm fan, with ventilation positioned above and below the front panel glass door, helping to keep dust out of the rack while ensuring a cool operating environment for your valuable equipment.

To ensure optimum security and prevent tampering with the enclosed equipment, the cabinet/rack features a lockable acrylic front door that can be removed entirely or installed to open to the left or right as needed.

Certifications, Reports and Compatibility



Applications

- Install rack equipment over doorways, or in tight spaces like server closets
- Mount networking and telecommunication equipment to the wall
- Securely protect and wall mount sensitive rack mountable equipment

Features

- **2-Post 6U RACK CABINET:** Wall-Mount Server Rack with a maximum mounting depth of 11.2" (28.5cm) is ideal for installing network switches, patch panels and other rackmount equipment in your warehouse, home / office, store location or server room
- **EASY ACCESS:** Wall-mount data rack features an enclosed and lockable rack design with easy access to the rear of the mounted devices; Small locking server cabinet with reversible and removable front door and removable side panels
- **BUILT TO LAST:** The 6U wall-mounted network cabinet is designed to provide a tough and rugged housing; This wall mount rack cabinet is constructed of heavy-duty steel for ultimate durability with a maximum weight capacity of 110lb (50kg)
- **FULLY ASSEMBLED:** Network cabinet ships fully assembled with 20x M5 screws and cage nuts to mount your IT equipment; Wall-mount equipment cabinet is EIA/ECA-310-E Compliant
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this IT rack enclosure is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	Lifetime
Wallmountable	Yes
Rack Type	2-Post
Frame Type	Enclosed Cabinet
U Height	6U
Special Features	Ships Fully Assembled Wall-Mountable
Mounting Rail Profile	L-Shape
Fan Options	One Fan Included: 120 mm + One Optional Fan: 120 mm
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

Performance

Airflow Rate	82 CFM
Audible Noise	45 dBA @ 1 Meter
Weight Capacity	110.2 lb [50 kg]

Physical Characteristics

Color	Black
Front Door Construction	Steel w/ Window
Front Door Features	Secure Key Lock with Removable Front Door
Side Panel Construction	Steel

Product Measurements

Internal Width	21.7 in [55 cm]
Internal Depth	15.7 in [40 cm]
Product Length	15.7 in [40.0 cm]
Product Width	22.0 in [56.0 cm]
Product Height	13.0 in [33.0 cm]
Weight of Product	27.7 lb [12.6 kg]

Maximum Mounting Depth 11.8 in [30 cm]

Packaging Information

Flat Pack (Assembly Required)	No
Package Length	26.4 in [67.0 cm]
Package Width	19.7 in [50.0 cm]
Package Height	17.3 in [44.0 cm]
Shipping (Package) Weight	33.5 lb [15.2 kg]

What's in the Box

Included in Package	1 - 6U Wallmount Cabinet
	1 - Set of Keys
	20 - M5 Screws
	20 - M5 Cage Nuts

**Warranty
Information**

Warranty Lifetime

**Product appearance and specifications are subject to change without notice.*

