

Customer Information Sheet

DRAWING No.: G125-MCXXX68M3-XXXXL



IF IN DOUBT - ASK

(C)

NOT TO SCALE


THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm



CONTACT No.	WIRE COLOUR
1	BLACK
2	BROWN
3	RED
4	ORANGE
5	YELLOW
6	GREEN
7	BLUE
8	VIOLET
9	GREY
10	WHITE

WIRE COLOURS REPEAT IN ABOVE ORDER FOR CONNECTOR ASSEMBLIES OVER 10 CONTACTS.



NOTES:

1. CABLE ASSEMBLIES WILL BE BULK PACKED IN BAGS.
2. CUSTOM LENGTH CABLE ASSEMBLIES CAN BE PRODUCED FROM 60mm TO 9999mm.
3. FOR COMPLETE SPECIFICATION SEE COMPONENT SPECIFICATIONS C049XX AND C125XX (LATEST ISSUES).

DIMENSION	MEASUREMENT
DIM 'A'	(TOTAL No. OF CONTACTS - 2) x 0.625 + 7.80
DIM 'B'	(TOTAL No. OF CONTACTS - 2) x 0.625 ± 0.20
DIM 'D'	(TOTAL No. OF CONTACTS - 2) x 0.625 + 2.00
DIM 'E'	(TOTAL No. OF CONTACTS - 2) x 0.625 + 12.7

EXAMPLE PART No.
12 CONTACT CONNECTOR WITH 150mm OF 26AWG WIRE = G125-MC11268M3-0150L
50 CONTACT CONNECTOR WITH 450mm OF 28AWG WIRE = G125-MC25068M3-0450L



HARWIN

www.harwin.com
technical@harwin.com

ORDER CODE:

G125-MCXXX68M3-XXXXL

26 AWG = 1
28 AWG = 2
TOTAL No. OF CONTACTS:
06, 10, 12, 16,
20, 26, 34, 50

DIM 'C' LENGTH:
0060 = 60mm MIN
9999 = 9999mm MAX

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.	TOLERANCES X. = ±1mm X.X = ±0.50mm X.XX = ±0.20mm X.XXX = ±0.01mm ANGLES = ±5° UNLESS STATED	MATERIAL: SEE ABOVE	TITLE: GECKO SL MALE CRIMP CONNECTOR WITH PIGTAIL
	FINISH: SEE ABOVE S/AREA: mm ²	DRAWING NUMBER: G125-MCXXX68M3-XXXXL SHT 2 OF 2	

RTP	3	22.03.21	30101
NAME	ISS.	DATE	CN/CO
APPROVED:	R. PORTLOCK		
CHECKED:	M. PLESTED		
DRAWN:	M. PLESTED		
CUSTOMER REF.:			
ASSEMBLY DRG:			