

4-Post 9U Mobile Open Frame Server Rack, Four Post Network Rack with Wheels, 19" Rolling Rack for Home/Office Narrow Floor Spaces, Small Data Rack for Computer/AV/IT Equipment - TAA Compliant

**Product ID:** RK960CP



This 9U portable server rack lets you store your server, network and telecommunications equipment in a sturdy mobile rack that has a fixed depth of 23.4 inches (59.5cm). This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

With built-in handles and four swiveling casters, this mobile rack is easy to transport around your server room, office or studio. Its increased mobility makes this cabinet the ideal solution for telecommunication racks that need to interface with different equipment around your workspace.

The server rack features heavy-gauge mounting rails to ensure a stable installation platform. This durable 4-post rack supports a static loading capacity of up to 297lb (135kg), and is compliant with several industry rack standards (EIA/ECA-310, IEC 60297, DIN 41494), providing a universal design that's compatible with most rack equipment.

Save time and hassle with a rack that's easy to put together. With its easy four-step assembly process, you can set this portable rack up in minutes.

## Certifications, Reports and Compatibility



## Applications

- Create a portable video editing and production rack that you can move around your studio to interface with different equipment

- Store this mobile rack beneath a table or bench in small offices or workspaces
- Mount equipment in technology shops and repair centers where security is required

## Features

- **MAXIMUM PORTABILITY:** built-in handles and four swiveling casters make this the ideal mobile AV / Data equipment rack to interface with other equipment around your workspace; Ideal for utility/server closets or narrow home / office spaces
- **EASY ASSEMBLY:** Rolling network rack with easy-to-follow assembly instructions; Compact flat-pack shipping to avoid damage and facilitate installation; Only 18.8in / 47.7cm high (without casters) or 22.1in / 56.2cm (with casters); EIA/ECA-310-E Compliant
- **STURDY DESIGN:** The server room rack features heavy-gauge mounting rails to ensure a stable installation platform; This 4-post rack supports a loading capacity of up to 220lb/100kg (Rolling) or 297lb/135kg (Stationary); Max mounting depth 23.4" (59.5cm)
- **HARDWARE INCLUDED:** 19" Open frame small computer / data rack includes cage nuts and screws to mount equipment, bracket and panel screws, easy to read Units (U) and required assembly tools
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this TAA Compliant server rack is backed for 2-years, including free lifetime 24/5 multi-lingual technical assistance

---

### Hardware

Warranty	2 Years
Wallmountable	No
Rack Type	4-Post
Frame Type	Enclosed Cabinet
U Height	9U
Special Features	Casters (Included)
	Easy Assembly
	U-Markings
Mounting Rail Profile	L-Shape
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

---

### Performance

Weight Capacity	297.7 lb [135 kg]
-----------------	-------------------

(Stationary)

Weight Capacity for Racks 220.5 lb [100 kg]  
(Rolling)

---

**Special Notes / Requirements**

Note	Dynamic Load Capacity 100.00 kg (220.46 lbs)
	Static Load capacity 135.00 kg (297.62 lbs)

---

**Physical Characteristics**

Color	Black
-------	-------

---

**Product Measurements**

Product Length	23.8 in [60.5 cm]
Product Width	20.5 in [52.0 cm]
Product Height	19.1 in [48.4 cm]
Weight of Product	53.1 lb [24.1 kg]
Maximum Mounting Depth	23.4 in [59.5 cm]
Product Height with Casters	22.4 in [56.9 cm]

---

**Packaging Information**

Flat Pack (Assembly Required)	Yes
Package Length	33.0 in [83.7 cm]
Package Width	28.7 in [72.9 cm]
Package Height	6.3 in [16.0 cm]
Shipping (Package) Weight	62.8 lb [28.5 kg]

---

**What's in the Box**

Included in Package	2 - Side panel with handles
	1 - Top panel
	1 - Bottom panel

8 - Plastic cornercaps  
32 - M5 (10 mm)Phillips flat-headscrew  
24 - M3 (8 mm)Phillips flat-headscrew  
2 - 2.5 in. caster  
2 - 2.5 in. brakecaster  
16 - M5 (15 mm)bracket screws  
50 - M5 (12 mm)panel screws  
50 - M5 cage nut  
1 - Cage nut tool  
1 - Phillipsscrewdriver  
1 - Phillips bit  
1 - Instruction manual

---

**Warranty  
Information**

Warranty	2 Years
----------	---------

---

*\*Product appearance and specifications are subject to change without notice.*

