


20in Slimline SATA to SATA with LP4 Power Cable Adapter

Product ID: SLSATAF20



The SLSATAF20 Slimline SATA to SATA with LP4 Power Cable (20-inch) features a SATA data receptacle and a LP4 power connection on one end, and a Slimline Serial ATA receptacle on the other - allowing you to connect a slim SATA drive to a computer motherboard that does not have a Slimline connection available.

Supporting full SATA 3.0 bandwidth of up to 6Gbps when used with SATA 3.0 compliant drives, this innovative adapter cable provides you with the connections needed to simplify the migration to Slimline SATA-equipped drives.

Constructed of only top quality materials and designed for optimum performance and reliability the SLSATAF20 is backed by our lifetime warranty.

Certifications, Reports and Compatibility



Applications

- Add a Slimline optical drive to a desktop PC

Features

- 1x SATA connector
- 1x LP4 power connector
- 1x Slimline SATA connector

- Supports full SATA 3.0 6Gbps bandwidth
- Compatible with Slimline SATA optical drives
- Provides 20" in cable length

Hardware

Warranty	Lifetime
Cable Jacket Material	PVC - Polyvinyl Chloride

Performance

Type and Rate	SATA III (6 Gbps)
---------------	-------------------

Connector(s)

Connector A	1 - Slimline SATA (13 pin, Data & Power)
Connector B	1 - LP4 (4 pin; Large Drive Power)
	1 - SATA (7 pin, Data)

Physical Characteristics

Color	Red
Cable Length	20.0 in [508 mm]
Product Length	20.0 in [50.8 cm]
Product Width	0.6 in [1.4 cm]
Product Height	0.2 in [6.0 mm]
Weight of Product	0.8 oz [22.0 g]

Packaging Information

Package Quantity	1
Package Length	5.3 in [13.4 cm]
Package Width	5.0 in [12.6 cm]
Package Height	0.7 in [1.9 cm]
Shipping (Package) Weight	1.0 oz [28.0 g]

What's in the Box

Included in Package	1 - 20in Slimline SATA to SATA with LP4 Power Cable Adapter
---------------------	---

**Warranty
Information**

Warranty	Lifetime
----------	----------

****Product appearance and specifications are subject to change without notice.***