

3ft (91cm) USB-C Charging Cable, Charge & Sync, 240W (5A) PD EPR, USB 2.0 Laptop Charger Cable, USB-IF Certified , TPE Jacket - Black USB C Charging Cord

Product ID: USB2EPR3F



Connect a charger to a USB Power Delivery (PD) 3.1-enabled device, using this USB-C Charging Cable. The USB-C charger cord facilitates up to 240W of USB-C Extended Power Range (EPR) Power Delivery and 5A output for fast charging. It supports USB 2.0 (480Mbps) throughput for general file transfer.

Designed for frequent use, the USB-C EPR Charging Cable features a rugged TPE outer jacket for increased wear resistance. The durable nickel-plated connectors are rated to operate beyond 10,000 insertion cycles, enhancing its durability and longevity.

Charge a USB-C device with a USB-C wall charger, car charger, or power bank. The 3-foot (0.9 meter) USB Type-C cable is the ideal length for desk and mobile workstations, commuters, in-car use or to reduce clutter when syncing with a USB-C laptop.

With up to 5A of output, the USB-C Charger Cord supports up to 240W of Power Delivery to charge a USB-C laptop, or fast charge a tablet or smartphone. To use, connect the cable from a USB-C laptop to a USB-C wall charger.

Certifications, Reports and Compatibility



Applications

- Ideal for high-power USB-C devices
- USB-IF Certified for guaranteed reliability

Features

- **USB-C EPR CHARGING CABLE:** USB Type-C cable supports Power Delivery 3.1 Extended Power Range (EPR); Up to 240W output for charging high-performance USB-C laptops and devices; Connects to a USB-C wall charger, power bank, or external USB-C hub
- **USB-IF CERTIFIED:** The USB C Cable is USB-IF certified with integrated E-marker chip, for consistent Power Delivery output to USB-C hosts and peripherals; When using certified cables, reliable performance and compatibility is guaranteed
- **QUALITY CONSTRUCTION:** Nickel-plated connectors rated beyond 10,000 insertion cycles; 30AWG wire tested to withstand 120° bends; Braided Aluminum shield for enhanced EMI protection; Durable TPE outer jacket is halogen-free and RoHS compliant
- **APPLICATIONS:** Compatible with USB-C Power Delivery-enabled devices; Ideal for high-power laptops requiring EPR charging, including 16in MacBook Pro M3 Pro/M3 Max; Supports USB 2.0 for general use, including file transfer and device synchronization
- **PERFORMANCE:** 240W/5A PD 3.1 EPR, 48V; Backward Compatible w/140W/100W/60W; USB 2.0 Type-C (480Mbps); Length: 3-foot (0.9-meter) cable; Color: Black; O.D.: 0.16in (4.0mm); TPE Jacket w/Braided Aluminum Shield; NOTE: USB-C video (DP Alt Mode) is not supported

Hardware

| | |
|---------------------------|--------------------------------|
| Warranty | Lifetime |
| Active or Passive Adapter | Passive |
| Connector Plating | Nickel |
| Cable Jacket Material | TPE - Thermoplastic Elastomers |
| Cable Shield Material | Aluminum-Mylar Foil with Braid |
| Cable Type | Passive Copper Cable |

Performance

| | |
|----------------------------|--------------------------------------|
| Maximum Data Transfer Rate | 480Mbps |
| Type and Rate | USB 2.0 - 480 Mbit/s |
| MTBF | Rated beyond 10,000 insertion cycles |

Connector(s)

| | |
|-------------|---|
| Connector A | 1 - USB Type-C (24-pin) USB 2.0 (480Mbps) |
| Connector B | 1 - USB Type-C (24-pin) USB 2.0 (480Mbps) |

Special Notes / Requirements

| | |
|------|--|
| Note | USB-C video (DP Alt Mode) is not supported |
|------|--|

Power

| | |
|----------------|-------------|
| Power Source | Bus Powered |
| Power Delivery | 240W |
| Input Current | 5A |

Environmental

| | |
|-----------------------|-------------------------|
| Operating Temperature | -10 ~ 55 (14F to 131F) |
| Storage Temperature | -25 ~ 70 (-13F to 158F) |
| Humidity | 0% ~ 95% |

Physical Characteristics

| | |
|-------------------|-------------------|
| Color | Black |
| Connector Style | Straight |
| Wire Gauge | 30 AWG |
| Material | Polyamide Resin |
| Cable Length | 3.0 ft [0.9 m] |
| Cable OD | 0.2 in [4 mm] |
| Product Length | 36.5 in [92.8 cm] |
| Product Width | 0.5 in [1.2 cm] |
| Product Height | 0.3 in [6.4 mm] |
| Weight of Product | 0.0 oz [0.0 g] |

Packaging Information

| | |
|--------------------|------------------|
| Package Length | 4.6 in [11.6 cm] |
| Package Width | 5.0 in [12.6 cm] |
| Package Height | 0.6 in [1.6 cm] |
| Shipping (Package) | 1.4 oz [40.0 g] |

Weight

What's in the Box

| | |
|---------------------|----------------------------------|
| Included in Package | 1 - 3ft USB-C Charging Cable M/M |
|---------------------|----------------------------------|

**Warranty
Information**

| | |
|----------|----------|
| Warranty | Lifetime |
|----------|----------|

**Product appearance and specifications are subject to change without notice.*

