

# CRM-91HE | Multifunction time relay with external potentiometer

5 YEAR  
WARRANTY



EAN code  
CRM-91HE/UNI: 8595188118958  
CRM-91HE/UNI + potentiometer: 8595188142052  
Potentiometer: 8595232367967

## Technical parameters


CRM-91HE	
Number of functions:	10
Supply terminals:	A1 - A2
Supply voltage:	AC/DC 12 - 240 V (AC 50-60 Hz)
Consumption (max.):	3 VA/1.7 W
Max. dissipated power:	4 W (Un + terminals)
Supply voltage tolerance:	-15 %; +10 %
Supply indication:	green LED
Time ranges:	0.1 s - 10 days
Time setting:	rotary switch, external potentiometer
Time deviation:	5 % - mechanical setting
Repeat accuracy:	0.2 % - set value stability
Temperature coefficient:	0.01 %/°C, at = 20°C (0.01%/°F, at = 68°F)
Output	
Contact type:	1x changeover/SPDT (AgNi/Silver Alloy)
Current rating:	16 A/AC1; 1 HP/240 Vac, 1/2 HP/120 Vac; PD. B300
Breaking capacity:	4000 VA/AC1, 384 W/DC1
Inrush current:	30 A/<3 s
Switching voltage:	250V AC/24V DC
Output indication:	multifunction red LED
Mechanical life:	10.000.000 ops.
Electrical life (AC1):	100.000 ops.
Controlling	
Control voltage:	AC/DC 12 - 240 V (AC 50-60 Hz)
Consumption of input:	AC 0.025-0.2 VA/DC 0.1-0.7 W
Load between S-A2:	Yes
Glow-tubes:	No
Control. terminals:	A1-S
Impulse length:	min. 25 ms/max. unlimited
Reset time:	max. 150 ms
Other information	
Operating temperature:	-20 .. +55 °C (-4 .. 131 °F)
Storage temperature:	-30 .. +70 °C (-22 .. 158 °F)
Dielectrical strength:	AC 4 kV (supply - output)
Operating position:	any
Mounting:	DIN rail EN 60715
Protection degree:	IP40 from front panel/IP20 terminals
Overtoltage category:	III.
Pollution degree:	2
Cross-wire section - solid/stranded with ferrule (mm <sup>2</sup> ):	max. 1x 2.5, 2x 1.5/ max. 1x 2.5 (AWG 12)
Dimensions:	90 x 17.6 x 64 mm (3.5" x 0.7" x 2.5")
Weight:	75 g (2.6 oz)
Standards:	EN 61812-1

## Technical parameters


Potentiometer	
Potentiometer:	5 - 150kΩ, linear
Protection degree:	IP 65 front side / IP20 f back side
Max. cable size (mm <sup>2</sup> ):	1.5 with sleeve/without sleeve max. 2.5 (AWG 12)
Weight:	16 g (0.6 oz.)
Dimensions:	see page Accessories

- Control by external control unit - potentiometer (can be placed/mounted for example on switch board doors or in panel).
- 10 functions:
  - 5 time functions controlled by supply voltage
  - 4 time functions controlled by control input
  - 1 function of latching relay.
- Possible to connect external potentiometer - max. distance 10 m (32.8 ft.) from relay.


## Description



## Connection



## Symbol



## Function




### ON DELAY

When the input voltage  $U$  is applied, timing delay  $t$  begins. Relay contacts  $R$  change state after time delay is complete. Contacts  $R$  return to their shelf state when input voltage  $U$  is removed. Trigger switch is not used in this function.




### INTERVAL ON

When input voltage  $U$  is applied, relay contacts  $R$  change state immediately and timing cycle begins. When time delay  $t$  is complete, contacts return to shelf state. When input voltage  $U$  is removed, contacts will also return to their shelf state. Trigger switch is not used in this function.




### FLASHER - OFF first

When input voltage  $U$  is applied, time delay  $t$  begins. When time delay  $t$  is complete, relay contacts  $R$  change state for time delay  $t$ . This cycle will repeat until input voltage  $U$  is removed. Trigger switch is not used in this function.




### FLASHER - ON first

When input voltage  $U$  is applied, relay contacts  $R$  change state immediately and time delay  $t$  begins. When time delay  $t$  is complete, contacts return to their shelf state for time delay  $t$ . This cycle will repeat until input voltage  $U$  is removed. Trigger switch is not used in this function.




### OFF DELAY

Input voltage  $U$  must be applied continuously. When trigger switch  $S$  is closed, relay contacts  $R$  change state. When trigger switch  $S$  is opened, delay  $t$  begins. When delay  $t$  is complete, contacts  $R$  return to their shelf state. If trigger switch  $S$  is closed before time delay  $t$  is complete, then time is reset. When trigger switch  $S$  is opened, the delay begins again, and relay contacts  $R$  remain in their energized state. If input voltage  $U$  is removed, relay contacts  $R$  return to their shelf state.




### SINGLE SHOT

Upon application of input voltage  $U$ , the relay is ready to accept trigger signal  $S$ . Upon application of the trigger signal  $S$ , the relay contacts  $R$  transfer and the preset time  $t$  begins. During time-out, the trigger signal  $S$  is ignored. The relay resets by applying the trigger switch  $S$  when the relay is not energized.




### SINGLE SHOT falling edge

Upon application of input voltage  $U$ , the relay is ready to accept trigger signal  $S$ . Upon application of the trigger signal  $S$ , the relay contacts  $R$  transfer and the preset time  $t$  begins. At the end of the preset time  $t$ , the relay contacts  $R$  return to their normal condition unless the trigger switch  $S$  is opened and closed prior to time out  $t$  (before preset time elapses). Continuous cycling of the trigger switch  $S$  at a rate faster than the preset time will cause the relay contacts  $R$  to remain closed. If input voltage  $U$  is removed, relay contacts  $R$  return to their shelf state.




### ON/OFF DELAY

Input voltage  $U$  must be applied continuously. When trigger switch  $S$  is closed, time delay  $t$  begins. When time delay  $t$  is complete, relay contacts  $R$  change state and remain transferred until trigger switch  $S$  is opened. If input voltage  $U$  is removed, relay contacts  $R$  return to their shelf state.



### MEMORY LATCH

Input voltage  $U$  must be applied continuously. Output changes state with every trigger switch  $S$  closure. If input voltage  $U$  is removed, relay contacts  $R$  return to their shelf state.



### PULSE GENERATOR

Upon application of input voltage  $U$ , a single output pulse of 0.5 seconds is delivered to relay after time delay  $t$ . Power must be removed and reapplied to repeat pulse. Trigger switch is not used in this function.