


<https://www.wago.com/216-1543>



Similar to illustration

Strip length	13.5 ... 14.5 mm / 0.53 ... 0.57 inches
Metric cross-section of the twin ferrule	2 x 1,5 mm ²
Cross-section (AWG) of twin ferrule	2 x 16 AWG

Total length (L)	20 mm
Wall thickness of crimp sleeve (W2)	0.15 mm
Wall thickness (plastic collar W1)	0.3 mm
Inner dimension of small plastic collar (D1)	3.6 mm
Inner dimension plastic collar large (D)	6.5 mm
Crimp length (length of sleeve L1)	12 mm
Diameter crimp sleeve inside (D2)	2.35 mm

Plastic collar	Standard collar
----------------	-----------------

Color	black
Weight	0.2 g



Commercial data		
PU (SPU)	1000 pcs	
Packaging type	Bag	
Country of origin	DE	
GTIN	4055143642811	
Customs tariff number	85369010000	

Product Classification		
UNSPSC	39121405	
ETIM 9.0	EC000005	
ETIM 10.0	EC000005	
ECCN	NO US CLASSIFICATION	

Environmental Product Compliance		
RoHS Compliance Status	Compliant, No Exemption	

Downloads


Environmental Product Compliance

Compliance Search

Environmental Product Compliance 216-1543

↓

Installation Notes



A perfect gas-tight crimp – both electrically and mechanically reliable