



Data Sheet | Item Number: 280-502/281-588

Component terminal block; double-deck; with end plate; with varistor; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm²; CAGE CLAMP®; gray


<https://www.wago.com/280-502/281-588>



Color: ■ gray

Similar to illustration

Similar to illustration



Short description:

This component terminal block with surge suppression device, end plate and direct connection to the DIN-35 rail is equipped with a varistor.

Features:

- Protect your system against overvoltage
- Slim, space-saving design
- Control operational costs by preventing expensive, unplanned downtime
- High operational reliability and system uptime

Notes

Safety Information

- Installation must be performed by qualified personnel only.
- The DIN-rail must be grounded.
- The input current must be protected by a suitable fuse.
- Protection against contact with stored charges must be ensured.
- Do not insert or remove pluggable modules when energized.
- The IP20 protection rating must be maintained in the assembled state or when using an end/intermediate plate compatible with the rail-mount terminal block.



Electrical data		
Nominal operating voltage		230 VAC
Maximum continuous voltage		275 VAC
Rated continuous current		20 A
Nominal discharge current (8/20 µs) (line)		1 kA
Discharge current (max.)		4.5 kA
Protection level (8/20 µs)		≤ 710 VAC
Capacitance		≤ 320 pF

Safety and protection		
Protection type		IP20

Connection Data		
Wiring direction		Front-entry wiring
Connections (number)		2
Connection technology		CAGE CLAMP®
Solid conductor		0.08 ... 2.5 mm ² / 28 ... 14 AWG
Fine-stranded conductor		0.08 ... 2.5 mm ² / 28 ... 14 AWG
Strip length		8 ... 9 mm / 0.31 ... 0.35 inches

Physical data		
Width		10 mm / 0.394 inches
Height		64 mm / 2.52 inches
Depth from upper-edge of DIN-rail		39.5 mm / 1.555 inches

Mechanical data		
Design		with end plate; with direct connection to DIN-rail
Mounting type		DIN-35 rail

Material data		
Color		gray
Insulation material (main housing)		Polyamide (PA66)
Material group		I
Flammability class per UL94		V0
Fire load		0.256 MJ
Weight		13.1 g

Environmental requirements		
Ambient temperature (operation)		-25 ... +70 °C
Processing temperature		-35 ... +85 °C
Operating altitude (max.)		2000 m

Product Group	1 (Rail Mounted Terminal Blocks)
PU (SPU)	50 (1) pcs
Packaging type	Box
Country of origin	DE
GTIN	4045454368401
Customs tariff number	85369010000

UNSPSC	39121410
eCl@ss 10.0	27-14-11-27
eCl@ss 9.0	27-14-11-27
ETIM 9.0	EC000903
ETIM 10.0	EC000903
ECCN	NO US CLASSIFICATION

RoHS Compliance Status	Compliant, No Exemption
------------------------	-------------------------

Declarations of conformity and manufacturer's declarations

Approval	Standard	Certificate Name
EU-Declaration of Conformity WAGO GmbH & Co. KG	-	-
UK-Declaration of Conformity WAGO GmbH & Co. KG	-	-

Environmental Product Compliance	
Compliance Search	
Environmental Product Compliance 280-502/281-588	



Documentation

Bid Text			
280-502/281-588	19.02.2019	xml 3.39 KB	
280-502/281-588	11.02.2015	doc 26.00 KB	

CAD/CAE-Data

CAD data	CAE data
2D/3D Models 280-502/281-588	EPLAN Data Portal 280-502/281-588
	WSCAD Universe 280-502/281-588
	ZUKEN Portal 280-502/281-588

1 Compatible Products

1.1 Optional Accessories

1.1.1 Insulation stop

1.1.1.1 Insulation stop



Item No.: 280-470
Insulation stop; 0.08 - 0.2 mm² "s" (0.14 mm² "f-st"); 5 pieces/strip; white



Item No.: 280-471
Insulation stop; 0.25 - 0.5 mm²; 5 pieces/strip; light gray



Item No.: 280-472
Insulation stop; 0.75 - 1 mm²; 5 pieces/strip; black

1.1.2 Jumper

1.1.2.1 Jumper



Item No.: 280-492
Jumper; 2-way; insulated; gray

1.1.3 Marking

1.1.3.1 Marker



Item No.: 2009-145
Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; white



Item No.: 248-501
Mini-WSB marking card; as card; not stretchable; plain; snap-on type; white



1.1.4 Tool

1.1.4.1 Operating tool



Item No.: 210-720
Operating tool; Blade: 3.5 x 0.5 mm; with a partially insulated shaft; multicoloured