

Special



Image for illustrative purpose only

Summary

[Request a quote](#)

00and01Coaxial en

Customer Drawing

Nb of contacts Coax	1
Locking system	Push-pull
Size	00
Suggested matching part	ERA.00.250.CTL
Series	00 - NIM-CAMAC

Technical details

Electrical Configuration

Nb of contacts Coax	1
Contact Termination Coax - Conductor fixing	Solder
Insert configuration value	0.25 - 1 Coax (50 Ohm)
Footprint IPC Class3 compatibility	No
Insulator	T: PTFE
Rated current	4 A
Impedance	50 Ohms
VSWR	$1.09 + 0.11 * f/\text{GHz}$
Vtest	2100 V (AC), 3000 V (DC)
Contact Dia.	0.7 mm (0.03in)

Form & Material

Shell style / Model id	ABF - Adapter from LEMO plug to BNC receptacle
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	Circular, male
Colour	Grey
Weight	8.18 g

Environment

Environmental sealing (IP rating)	IP50
Endurance	>1000 mating cycles
F ret (min)	100 N
Salt Spray Corrosion	>1000 hr

Cable fixation

Cable termination protection	Standard back nut (no additional protection)
------------------------------	--