

*Image for illustrative purpose only*

## Summary

[Request a quote](#)

Number of contacts Low Voltage	10
Nb of contacts Coax	1
Wire Size/AWG	30 - 22
Gender	Standard
Socket / Receptacle	Socket / Receptacle - Fixed Panel Front Mounted
Locking system	Push-pull
Size	2P
Suggested matching part	<a href="#">CAB.810.GLA.C521</a> <a href="#">CAB.810.GLA.C921G</a>
Series	REDEL P - Push-Pull

# Technical details

## Electrical Configuration

Number of contacts Low Voltage	10
Contact Termination Low voltage	Solder
Nb of contacts Coax	1
Contact Termination Coax - Conductor fixing	Crimp
Insert configuration value	2P.810 - 1 Coax (50 Ohm), 10 Low V.
Insulator	L: PEEK for solder contacts
Rated current	5 A
Impedance	50 Ohms
Test voltage contact-contact	1.77 (kV DC)
Air clearance	0.9 mm
Creepage distance	0.9 mm
Contact Dia.	0.7
Wire Size/AWG	30 - 22
Gender	Standard

## Form & Material

Shell style / Model id	CL - Fixed receptacle, nut fixing
Socket / Receptacle	Fixed Panel Front Mounted
Housing material	PSU (Polysulfone), grey
Locking system	Push-pull
Keying	B: 3 keys (alpha=0, gamma=60, Plug: male contacts, Receptacle: female contacts)
Colour	Grey
Weight	7.24 g

## Environment

Technical domain	Energy and Industrial, Medical, Test and Measurement, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	IP50
Endurance	>5000 mating cycles
Temperature range	-50°C / +150°C

[https://www.lemo.com/int\\_en/solutions/redeI/redeI-p-push-pull/clb-810-gli1g.html](https://www.lemo.com/int_en/solutions/redeI/redeI-p-push-pull/clb-810-gli1g.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Dimensions

---

N	
mm.	23.8
in.	0.94

[https://www.lemo.com/int\\_en/solutions/redeI/redeI-p-push-pull/clb-810-gI1g.html](https://www.lemo.com/int_en/solutions/redeI/redeI-p-push-pull/clb-810-gI1g.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.