

Special



Image for illustrative purpose only

Summary

[Request a quote](#)

M series

Number of contacts Low Voltage	5
Gender	Reverse Gender
Socket / Receptacle	Socket / Receptacle - Fixed Panel Front Mounted
Locking system	Ratchet
Size	0M
Suggested matching part	FMT.0M.305.XLM
Series	M - Rugged Ratchet coupling

https://www.lemo.com/int_en/solutions/optima/m-ratchet-coupling/edt-0m-305-xld.html

LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Number of contacts Low Voltage	5
Contact Termination Low voltage	PCB - Straight
R (max)	6.1 mOhm
Insert configuration value	0M.305 - 5 Low Voltage
Footprint IPC Class3 compatibility	Yes
Class3 Productibility Level Compatibility	B (Moderate Design Producibility - Standard)
Insulator	L: PEEK
Rated current	6.5 A
Test voltage (kV rms) Contact-contact	1.25
Test voltage (kV rms) Contact-shell	1
Contact Dia.	0.7 mm (0.028in)
Gender	Reverse Gender

Form & Material

Shell style / Model id	ED - Fixed receptacle with square flange for printed circuit
Socket / Receptacle	Fixed Panel Front Mounted
Housing material	Aluminium (nickel plated [SAE AMS QQ N 290], anthracite color) shell and nut, other pieces bronze/brass
Locking system	Ratchet
Keying	T: 3 keys (beta=135, gamma=90, plug: female contacts, receptacle: male contacts)
Colour	Grey
Weight	3.55 g



https://www.lemo.com/int_en/solutions/optima/m-ratchet-coupling/edt-0m-305-xld.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Environment

Technical domain	Motorsport, Security and Defence, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	IP68
Endurance	3000 mating cycles
Temperature range	-20°C / +200°C (max. temperature valid for short periods of use.)
EMI Shielding EIA 364-66A	≥ 80 dB (1 GHz), ≥ 70 dB (3 GHz), ≥ 58 dB (6 GHz), ≥ 40 dB (10 GHz)
Gunfire vibration	25 Hz - 2000 Hz, 3 axis (Apache helicopter)
Humidity (max)	21 days at 95%
Lighting strike EIA 364-76	10K amps - 6 times
Shock Resistance	300 g [3 ms]
Thermal shock	5 cycles: -65°C to +150°C
Vibration-Random	37.8 g rms - 3 axes, 4 hr amb [50 Hz - 2000 Hz]
Vibration-Sine	30 g, 3 axes, 12 hr [10 Hz - 2000 Hz]
Salt Spray Corrosion	max. 48 hr

Drawings



Dimensions

	A	B	C	G	H	K	Ls	Lr	N	P	SV
mm.	20.6	4.72	12.7	12.8	11	1.5	18.3	18.3	16	5.3	2.7
in.	0.81	0.19	0.5	0.5	0.43	0.06	0.72	0.72	0.63	0.21	0.11

https://www.lemo.com/int_en/solutions/optima/m-ratchet-coupling/edt-0m-305-xld.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Recommended By Lemo

Accessories	
Compatible cap	BGE.0M.200.XAZ

CAD

Documents	
PCB	Download
PCB Eagle	Download
Kicad	Download
PCB Altium	Download