




Click [here](#) for the 3D model.

General Information

Series	APL90
Dielectric	Polymer Aluminum
Description	Rectangular Aluminum Electrolytic
RoHS	Yes
Lead	Wire Leads
Qualifications	AEC-Q200
AEC-Q200	Yes
Halogen Free	Yes
Typical Component Weight	9.5 g
Notes	High vibration up to 20 g.
Shelf Life	156 Weeks

Specifications

Capacitance	660 uF
Tolerance	20%
Voltage DC	63 VDC, 72.45 VDC (Surge)
Temperature Range	-55/+125°C
Rated Temperature	125°C
Life	2000 Hrs (Rated Voltage And Ripple Current At 125C)
ESR	16 mOhms (10kHz 20C)
Ripple Current	6 Amps (10kHz 125C), 7.1 Amps (100kHz 125C), 15.4 Amps (10kHz 125C), 18.4 Amps (100kHz 125C)
Leakage Current	415.8 uA

Dimensions

L	36.4mm +/-0.5mm
L2	38mm +/-2mm
W	24mm +/-0.5mm
H	8mm +/-0.5mm
S	10mm +/-1mm
LL	42mm +/-2mm
LL2	40mm +/-2mm

Packaging Specifications

Packaging	Bulk
-----------	------