



Image for illustrative purpose only

Summary

[Request a quote](#)

[f series](#)

Number of contacts Low Voltage	5
Wire Size/AWG	24 - 20
Gender	Standard
Socket / Receptacle	Socket / Receptacle - Fixed Panel Rear Mounted
Locking system	Push-pull
Panel Drill Hole	M13
Jacket cable outside diameter [mm]	3.80 - 10.70 mm
Size	1F
Suggested matching part	FGN.1F.305.XLC
Series	F - Rugged Push-Pull

https://www.lemo.com/int_en/solutions/optima/f-rugged-push-pull/een-1f-305-xlm.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Number of contacts Low Voltage	5
Contact Termination Low voltage	Crimp
R (max)	4.8 mOhm
Insert configuration value	1F.305 - 5 Low Voltage
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	9 A
Vtest (contact-contact)	1300 V (AC), 1840 V (DC)
Vtest (contact-shell)	1550 V (AC), 2200 V (DC)
Contact retention	30 N
Max. Conductor	0.5 mm ² (AWG 20)
Min. Conductor	0.25 mm ² (AWG 24)
Bucket Dia.	1.1 mm (0.043in)
Contact Dia.	0.9 mm (0.035in)
Wire Size/AWG	24 - 20
Gender	Standard

Form & Material

Shell style / Model id	EE - Fixed receptacle, nut fixing (back panel mounting)
Socket / Receptacle	Fixed Panel Rear Mounted
Housing material	Aluminium (nickel plated [SAE AMS QQ N 290], anthracite color) shell and nut, other pieces bronze/brass
Locking system	Push-pull
Keying	3 keys (beta=165, gamma=30, plug: male contacts, receptacle: female contacts)
Colour	Grey
Weight	5.66 g
Panel Drill Hole	M13

https://www.lemo.com/int_en/solutions/optima/f-rugged-push-pull/een-1f-305-xlm.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.


Environment

Technical domain	Motorsport, Security and Defence
Environmental sealing (IP rating)	IP50
Endurance	1000 mating cycles
Temperature range	-15°C / +200°C (max. temperature valid for short periods of use.)
Climatic Category	15/200/21 (Aluminium shell)
Humidity (max)	<=95% [at 60 deg C /140 F]
Shock Resistance	100 g [6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	max. 48 hr

Cable fixation

Jacket cable outside diameter [mm]	3.80 - 10.70 mm
------------------------------------	-----------------

Drawings



Dimensions

	B	e	E	S3	S2	A	S1	P	N	M
mm.	15	M13x0.75	6.2	14	14	17	11.5	9.4	19	3.2
in.	0.59		0.24	0.55	0.55	0.67	0.45	0.37	0.75	0.13

Recommended By Lemo

Accessories

Replacement contact	EGG.0B.660.ZZM
Compatible cap	BRE.1F.200.XAV

https://www.lemo.com/int_en/solutions/optima/f-rugged-push-pull/een-1f-305-xlm.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Tools

Spanner 2	DCM.65.140.AZ
Positionner	DCE.91.090.BVM
Extraction tool	DCC.09.05B.LAG
Crimp tool	DPC.91.701.V

Cables

Cable PartNumber	Material	Colour	Cable image
CMN.05.T20.057PGZE		grey	
CMN.05.T20.057PNZE			
CMN.05.T20.057QGZE	TPR (medical)	Grey	
CMN.05.T22.051QGZE	TPR (medical)	Grey	
CMN.05.T28.029PGCE	PVC	GREY	
CMN.05.T28.029PGZE		grey	
CMN.05.T28.029PNCE	PVC	Black	
CMN.05.T28.029PNZE			
150250	PVC	Grey	
250500	PVC	Grey	
50090	PVC	Black	
50140	PVC	Grey	
5050	PVC	Black	

https://www.lemo.com/int_en/solutions/optima/f-rugged-push-pull/een-1f-305-xlm.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.