

Standard



Image for illustrative purpose only

Summary

[Request a quote](#)

[M series](#)

[Application leaflet Security Defence](#)

[Customer Drawing](#)

Number of contacts Low Voltage	8
Gender	Standard
Socket / Receptacle	Socket / Receptacle - Fixed Panel Front Mounted
Locking system	Ratchet
Panel Drill Hole	M14
Jacket cable outside diameter [mm]	6.50 - 13.00 mm
Size	2M
Suggested matching part	FGN.2M.308.XRC6

https://www.lemo.com/int_en/solutions/optima/m-ratchet-coupling/egn-2m-308-xrm6.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Number of contacts Low Voltage	8
Contact Termination Low voltage	Crimp
R (max)	4.8 mOhm
Insert configuration value	2M.308_6 - 6 (0.7 mm) + 2 (1.3 mm) Low Voltage
Insulator	R: PEEK (mixed multipole)
Rated current	0.7 mm : 7 A, 1.3 mm : 23 A
Test voltage contact-contact	2.45 kV DC
Test voltage contact-shell	2 kV DC
Contact retention	30 N
Bucket Dia.	6x0.87 mm, 2x1.6 mm
Contact Dia.	6x0.7 mm, 2x1.3 mm
Wire Size/AWG details	0.7 mm : 26-22, 1.3 mm : 20-16
Gender	Standard

Form & Material

Shell style / Model id	EG - Fixed receptacle, nut fixing
Socket / Receptacle	Fixed Panel Front Mounted
Housing material	Aluminium (nickel plated [SAE AMS QQ N 290], anthracite color) shell and nut, other pieces bronze/brass
Locking system	Ratchet
Keying	N: 3 keys (beta=165, gamma=30, plug: male contacts, receptacle: female contacts)
Colour	Grey
Weight	9.11 g
Panel Drill Hole	M14

https://www.lemo.com/int_en/solutions/optima/m-ratchet-coupling/egn-2m-308-xrm6.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Environment

Technical domain	Motorsport, Security and Defence, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	IP68
Endurance	3000 mating cycles
Temperature range	-20°C / +200°C (max. temperature valid for short periods of use.)
EMI Shielding EIA 364-66A	>= 80 dB (1 GHz), >=70 dB (3 GHz), >= 58 dB (6 GHz), >= 40 dB (10 GHz)
Gunfire vibration	25 Hz - 2000 Hz, 3 axis (Apache helicopter)
Humidity (max)	21 days at 95%
Lighting strike EIA 364-76	10K amps - 6 times
Shock Resistance	300 g [3 ms]
Thermal shock	5 cycles: -65°C to +150°C
Vibration-Random	37.8 g rms - 3 axes, 4 hr amb [50 Hz - 2000 Hz]
Vibration-Sine	30 g, 3 axes, 12 hr [10 Hz - 2000 Hz]
Salt Spray Corrosion	max. 48 hr

Cable fixation

Jacket cable outside diameter [mm]	6.50 - 13.00 mm
------------------------------------	-----------------

Recommended By Lemo

Contacts

Replacement contact	EGN.0M.655.ZZM
---------------------	--------------------------------

Caps

Compatible cap	BGE.2M.200.XAZ
Cap 2	BME.2M.200.XAZ

Tools

Positionner	DCE.91.070.3MVM
Positionner 2	DCE.91.130.5MVM
Extraction tool	DCF.93.131.4LT
Extraction tool 2	DCF.93.070.4LT
Crimp tool	DPC.91.701.V

https://www.lemo.com/int_en/solutions/optima/m-ratchet-coupling/egn-2m-308-xrm6.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.