



Image for illustrative purpose only

Summary

[Request a quote](#)

[f series](#)

Number of contacts Low Voltage	5
Gender	Standard
Socket / Receptacle	Socket / Receptacle - Fixed Panel Rear Mounted
Locking system	Push-pull
Size	0F
Suggested matching part	FGN.0F.305.XLC
Series	F - Rugged Push-Pull

https://www.lemo.com/int_en/solutions/optima/f-rugged-push-pull/ehn-0f-305-xln.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Number of contacts Low Voltage	5
Contact Termination Low voltage	PCB - Straight
R (max)	6.1 mOhm
Insert configuration value	0F.305 - 5 Low Voltage
Footprint IPC Class3 compatibility	Yes
Class3 Productibility Level Compatibility	A (General Design Producibility - Preferred)
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	6.5 A
Vtest (contact-contact)	1250 V (AC), 1770 V (DC)
Vtest (contact-shell)	1200 V (AC), 1700 V (DC)
Contact Dia.	0.7 mm (0.028in)
Gender	Standard

Form & Material

Shell style / Model id	EH - Fixed receptacle, nut fixing (back panel mounting, printed circuit mounting possible)
Socket / Receptacle	Fixed Panel Rear Mounted
Housing material	Aluminium (nickel plated [SAE AMS QQ N 290], anthracite color) shell and nut, other pieces bronze/brass
Locking system	Push-pull
Keying	3 keys (beta=165, gamma=30, plug: male contacts, receptacle: female contacts)
Colour	Grey
Weight	3.31 g

https://www.lemo.com/int_en/solutions/optima/f-rugged-push-pull/ehn-0f-305-xln.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.


Environment

Technical domain	Motorsport, Security and Defence
Environmental sealing (IP rating)	IP67
Endurance	1000 mating cycles
Temperature range	-15°C / +200°C (max. temperature valid for short periods of use.)
Climatic Category	15/200/21 (Aluminium shell)
Humidity (max)	<=95% [at 60 deg C /140 F]
Shock Resistance	100 g [6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	max. 48 hr

Cable fixation

Panel Drill Hole	M10
------------------	-----

Drawings



Dimensions

	e	E	B	A	S2	M	P	S1	N
mm.	M10x0.75	3	14	13	11	2.5	14.5	9	19
in.		0.12	0.55	0.51	0.43	0.1	0.57	0.35	0.75

Recommended By Lemo

Accessories

Compatible cap	BRE.0F.200.XAV
----------------	--------------------------------

https://www.lemo.com/int_en/solutions/optima/f-rugged-push-pull/ehn-0f-305-xln.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Documents

PCB	Download
PCB Eagle	Download
Kicad	Download
PCB Altium	Download