

Special

*Image for illustrative purpose only*

Summary

[Request a quote](#)

BKT series

Number of contacts Low Voltage	40
Wire Size/AWG	30 - 22
Gender	Standard
Socket / Receptacle	Socket / Receptacle - Fixed Panel Front Mounted
Locking system	Push-pull
Panel Drill Hole	M25
Jacket cable outside diameter [mm]	4.00 - 23.60 mm
Size	4B
Suggested matching part	FGG.4B.340.PLAD10B FGG.4B.340.PLAM62B
Series	B - Indoor keyed

Technical details

Electrical Configuration

Number of contacts Low Voltage	40
Contact Termination Low voltage	Solder
R (max)	6.1 mOhm
Insert configuration value	4B.340 - 40 Low Voltage
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	3 A
Vtest (contact-contact)	1.4 kV (DC)
Vtest (contact-shell)	1.4 kV (DC)
Max. Solid Conductor	0.34 mm ² (AWG 22)
Max. Stranded Conductor	0.34 mm ² (AWG 22)
Bucket Dia.	0.8 mm (0.031in)
Contact Dia.	0.7 mm (0.028in)
Wire Size/AWG	30 - 22
Gender	Standard

Form & Material

Shell style / Model id	EN - Fixed receptacle with grounding tab, nut fixing, PSU or PPSU outer shell
Socket / Receptacle	Fixed Panel Front Mounted
Housing material	PSU (Polysulfone) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	G: 1 key (alpha=0, plug: male contacts, receptacle: female contacts)
Weight	38.33 g
Panel Drill Hole	M25




Environment

Technical domain	Audio Video, Energy and Industrial, Medical, Semiconductor, Specialties and Other, Test and Measurement, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	IP50
Endurance	5000 mating cycles
Temperature range	-55°C / +250°C (max. temperature valid for short periods of use.)
Climatic Category	55/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	75 dB (10 MHz)
Shielding (min)	40 dB (1 GHz)
Shock Resistance	100 g [6 ms]
Vibration	15 g [10 Hz - 2000 Hz]

Cable fixation

Jacket cable outside diameter [mm]	4.00 - 23.60 mm
------------------------------------	-----------------

Drawings



Dimensions

	A	B	e	E	L max F1	L max F2	M	S1	S3
mm.	28	34	M25x1.0	12	34.5	38.5	2.5	23.5	30
in.	1.1	1.34		0.47	1.36	1.52	0.1	0.93	1.18

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/eng-4b-340-plib.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.