

Special

*Image for illustrative purpose only*

## Summary

[Request a quote](#)

### SE series

Number of contacts Low Voltage	2
Wire Size/AWG	30 - 22
Socket / Receptacle	Socket / Receptacle - Fixed Panel Rear Mounted
Locking system	Push-pull
Size	0S
Suggested matching part	<a href="#">FFA.0S.302.CYXC37</a>
Series	S - Indoor Stepped Insert

[https://www.lemo.com/int\\_en/solutions/originals/s-indoor-stepped-insert/erd-0s-302-cyz.html](https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/erd-0s-302-cyz.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Number of contacts Low Voltage	2
Insert configuration value	0S.302 - 2 Low Voltage
Insulator	Y: PEEK for crimp contacts
Rated current	10 A
Test voltage (kV DC)	1.6
Contact Dia.	0.9
Wire Size/AWG	30 - 22
Important recommendation	Contacts to be ordered separately

## Form & Material

Shell style / Model id	ERD - Fixed receptacle with two nuts (back panel mounting)
Socket / Receptacle	Fixed Panel Rear Mounted
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	Hermaphroditic keying (half moon insert) with female pin 1
Colour	Grey
Variant	Delivered without contact
Weight	4.48 g

## Environment

Technical domain	Audio Video, Energy and Industrial, Semiconductor, Test and Measurement
Environmental sealing (IP rating)	IP50
Endurance	5000 mating cycles
Temperature range	-55°C / +250°C (max. temperature valid for short periods of use.)
Climatic Category	55/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	75 dB (10 MHz)
Shielding (min)	40 dB (1 GHz)
Shock Resistance	100 g [ 6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

## Cable fixation

Panel Drill Hole	M9
------------------	----

## Drawings



## Dimensions

	<b>A</b>	<b>B</b>	<b>e</b>	<b>E</b>	<b>L</b>	<b>M</b>	<b>S1</b>	<b>S3</b>
mm.	12	12.5	M9x0.6	5.5	18.5	2.5	8.2	11
in.	0.47	0.49		0.22	0.73	0.1	0.32	0.43

# Recommended By Lemo

## Accessories

---

Compatible cap	BRE.0S.200.NAS
----------------	----------------

## Tools

---

Spanner 2	DCM.65.106.AZ4
-----------	----------------

Spanner wrench	Socket for torque wrench DCM.0S.M09.4
----------------	---------------------------------------

[https://www.lemo.com/int\\_en/solutions/originals/s-indoor-stepped-insert/erd-0s-302-cyz.html](https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/erd-0s-302-cyz.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.