



Image for illustrative purpose only

Summary

[Request a quote](#)

[unipole multipole](#)

| | |
|--------------------------------|---|
| Number of contacts Low Voltage | 12 |
| Wire Size/AWG | 32 - 24 |
| Socket / Receptacle | Socket / Receptacle - Fixed Panel Front Mounted |
| Locking system | Push-pull |
| Size | 2C |
| Suggested matching part | FFA.2C.312.CLAC67 |

Technical details

Electrical Configuration

| | |
|---------------------------------|-------------------------------|
| Number of contacts Low Voltage | 12 |
| Contact Termination Low voltage | Solder |
| R (max) | 6.1 mOhm |
| Insert configuration value | 2C.312 - 12 Low Voltage |
| Insulator | L: PEEK (UL 94 / V-0/1.5) |
| Rated current | 5 A |
| Vtest | 600 V (AC), 900 V (DC) |
| Max. Solid Conductor | 0.25 mm ² (AWG 24) |
| Max. Stranded Conductor | 0.14 mm ² (AWG 26) |
| Bucket Dia. | 0.6 mm (0.024in) |
| Contact Dia. | 0.7 mm (0.028in) |
| Wire Size/AWG | 32 - 24 |

Form & Material

| | |
|------------------------|---|
| Shell style / Model id | ERY - Fixed receptacle, protruding shell (screw fixing on the panel) |
| Socket / Receptacle | Fixed Panel Front Mounted |
| Housing material | Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces |
| Locking system | Push-pull |
| Keying | Hermaphroditic keying (half moon insert) with female pin 1 |
| Weight | 5.37 g |


Environment

| | |
|-----------------------------------|-------------------|
| Environmental sealing (IP rating) | IP50 |
| Endurance | 500 mating cycles |
| Salt Spray Corrosion | >1000 hr |

https://www.lemo.com/int_en/ery-2c-312-cl1.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Drawings



Dimensions

| A | L | e |
|-----|------|------|
| mm. | 14 | 15.6 |
| in. | 0.55 | 0.61 |

Cables

| Cable PartNumber | Material | Colour | Cable image |
|--------------------|----------|--------|-------------|
| CMN.12.T28.054PGZE | | grey | |
| CMN.12.T28.054PNZE | | | |
| 112240 | PTFE | White | |
| 112260 | PTFE | White | |
| 112280 | PVC | Black | |
| 12050 | PVC | Black | |
| 124080 | PVC | Grey | |
| 124084 | PVC | Black | |
| 212250 | PVC | Grey | |
| 212260 | PVC | Black | |