

Special



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

---

[BKT series](#)

---

[See video assembly instructions](#)

---

[Customer Drawing](#)

Number of contacts Low Voltage	40
Wire Size/AWG	26 - 22
Gender	Standard
Plug	Plug - Straight
Locking system	Push-pull
Jacket cable outside diameter [mm]	12.10 - 13.50 mm
Size	4B
Suggested matching part	<a href="#">EGG.4B.340.CLL</a>

[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/fgg-4b-340-cycd13.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fgg-4b-340-cycd13.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/fgg-4b-340-cycd13.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fgg-4b-340-cycd13.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Number of contacts Low Voltage	40
Contact Termination Low voltage	Crimp
R (max)	6.1 mOhm
Insert configuration value	4B.340 - 40 Low Voltage
Insulator	Y: PEEK for crimp contacts
Rated current	3 A
Vtest (contact-contact)	2 kV (DC)
Vtest (contact-shell)	1.9 kV (DC)
Contact retention	22 N
Max. Conductor	0.34 mm <sup>2</sup> (AWG 22)
Min. Conductor	0.14 mm <sup>2</sup> (AWG 26)
Bucket Dia.	0.8 mm (0.031in)
Contact Dia.	0.7 mm (0.028in)
Wire Size/AWG	26 - 22
Gender	Standard

## Form & Material

Shell style / Model id	FG - Straight plug, cable collet
Plug	Straight
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	G: 1 key (alpha=0, plug: male contacts, receptacle: female contacts)
Colour	Grey
Weight	118.52 g

## Environment

---

Technical domain	Audio Video, Energy and Industrial, Medical, Semiconductor, Specialties and Other, Test and Measurement, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	IP50
Endurance	5000 mating cycles
Temperature range	-55°C / +250°C (max. temperature valid for short periods of use.)
Climatic Category	55/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	75 dB (10 MHz)
Shielding (min)	40 dB (1 GHz)
Shock Resistance	100 g [ 6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

## Cable fixation

---

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	12.10 - 13.50 mm

## Recommended By Lemo

### Accessories

---

Replacement contact	<a href="#">FGG.4B.555.ZZC</a>
Compatible cap	<a href="#">BFG.4B.100.NAS</a>

### Tools

---

Spanner	<a href="#">DCP.91.045.TN</a>
Positionner	<a href="#">DCE.91.074.BVC</a>
Extraction tool	<a href="#">DCC.07.04B.LAG</a>
Crimp tool	<a href="#">DPC.91.701.V</a>

[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/fgg-4b-340-cycd13.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fgg-4b-340-cycd13.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# CAD

## Documents

---

Eplan

[Download](#)

[https://www.lemo.com/int\\_en/solutions/originals/b-indoor-keyed/fgg-4b-340-cycd13.html](https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/fgg-4b-340-cycd13.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.