

Special



Image for illustrative purpose only

Summary

[Request a quote](#)

[M series](#)

[Application leaflet Security Defence](#)

[See video assembly instructions](#)

Number of contacts Low Voltage	55
Wire Size/AWG	24 - 20
Gender	Standard
Plug	Plug - Straight
Locking system	Ratchet
Panel Drill Hole	M25
Jacket cable outside diameter [mm]	11.35 - 22.70 mm
Size	LM
Suggested matching part	PMW.LM.355.XLMT PHW.LM.355.XLMT
Series	M - Rugged Ratchet coupling

Technical details

Electrical Configuration

Number of contacts Low Voltage	55
Contact Termination Low voltage	Crimp
R (max)	4.8 mOhm
Insert configuration value	LM.355 - 55 (0.9 mm) Low Voltage
Insulator	L: PEEK
Rated current	3.5 A
Test voltage contact-contact	2.33 kV DC
Test voltage contact-shell	2.75 kV DC
Contact retention	30 N
Max. Conductor	0.5 mm ² (AWG 20)
Min. Conductor	0.25 mm ² (AWG 24)
Bucket Dia.	1.1 mm (0.043in)
Contact Dia.	0.9 mm (0.035in)
Wire Size/AWG	24 - 20
Gender	Standard

Form & Material

Shell style / Model id	FM - Straight plug, key (N) or keys (P, R, S, T, U, V, W and X) with knurled grip and mold stop
Plug	Straight
Housing material	Aluminium (nickel plated [SAE AMS QQ N 290], anthracite color) shell and nut, other pieces bronze/brass
Locking system	Ratchet
Keying	W: 5 keys (alpha=95, beta=115, gamma=35, delta=25, plug: male contacts, receptacle: female contacts)
Colour	Grey
Weight	32.22 g
Panel Drill Hole	M25




Environment

Technical domain	Motorsport, Security and Defence, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	IP68
Endurance	3000 mating cycles
Temperature range	-55°C / +200°C (max. temperature valid for short periods of use.)
EMI Shielding EIA 364-66A	>= 80 dB (1 GHz), >=70 dB (3 GHz), >= 58 dB (6 GHz), >= 40 dB (10 GHz)
Gunfire vibration	25 Hz - 2000 Hz, 3 axis (Apache helicopter)
Humidity (max)	21 days at 95%
Lighting strike EIA 364-76	10K amps - 6 times
Shock Resistance	300 g [3 ms]
Thermal shock	5 cycles: -65°C to +150°C
Vibration-Random	37.8 g rms - 3 axes, 4 hr amb [50 Hz - 2000 Hz]
Vibration-Sine	30 g, 3 axes, 12 hr [10 Hz - 2000 Hz]
Salt Spray Corrosion	max. 48 hr

Cable fixation

Cable termination protection	For overmolding
Fixation type	Mold stop (overmolding)
Jacket cable outside diameter [mm]	11.35 - 22.70 mm

Drawings



Dimensions

	A	B	C	D	F	Ls	Lr	M	P	X
mm.	28.5	23.9	28	22.7	25.8	31.6	31.6	10.6	3.4	7.6
in.	1.12	0.94	1.1	0.89	1.02	1.24	1.24	0.42	0.13	0.3

Recommended By Lemo

Contacts

Replacement contact

[FGN.0M.560.ZZC](#)

Caps

Compatible cap

[BMF.LM.100.XAV](#)

Tools

Positionner

[DCE.91.090.5MVC](#)

Extraction tool

[DCC.09.05B.LAG](#)

Crimp tool

[DPC.91.701.V](#)