



Image for illustrative purpose only

Summary

[Request a quote](#)

F series

Nb of contacts Thermocouple	2
Wire Size/AWG	30 - 22
Gender	Standard
Socket / Receptacle	Socket / Receptacle - Fixed Panel Rear Mounted
Locking system	Push-pull
Jacket cable outside diameter [mm]	3.80 - 9.00 mm
Size	0F
Series	F - Rugged Push-Pull

Technical details

Electrical Configuration

Nb of contacts Thermocouple	2
Contact Termination Thermocouple	Solder
Insert configuration value	0F.302 - 2 Low Voltage
Footprint IPC Class3 compatibility	No
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	10 A
ThC. Materials (P+/N-)	Chromel / Alumel
Contact Dia.	0.9
Wire Size/AWG	30 - 22
Gender	Standard

Form & Material

Shell style / Model id	PE - Straight receptacle, nut fixing (back panel mounting)
Socket / Receptacle	Fixed Panel Rear Mounted
Housing material	Aluminium (nickel plated [SAE AMS QQ N 290], anthracite color) shell and nut, other pieces bronze/brass
Locking system	Push-pull
Keying	3 keys (beta=150, gamma=60, plug: male contacts, receptacle: female contacts)
Colour	Grey
Weight	5.9 g

Environment

Technical domain	Motorsport, Security and Defence
Environmental sealing (IP rating)	IP67
Endurance	1000 mating cycles
Temperature range	-15°C / +200°C (max. temperature valid for short periods of use.)
Climatic Category	15/200/21 (Aluminium shell)
Humidity (max)	<=95% [at 60 deg C /140 F]
Shock Resistance	100 g [6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	max. 48 hr



https://www.lemo.com/int_en/solutions/optima/f-rugged-push-pull/pep-0f-302-xlk.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Cable fixation

Cable termination protection	Heatshrink
Fixation type	Heatshrink
Jacket cable outside diameter [mm]	3.80 - 9.00 mm
Panel Drill Hole	M10

Drawings



Dimensions

	M	A	B	L	E	e	C	S1	S2	X
mm.	2.5	13	9	26.7	6	M10x0.75	13	9	11	8
in.	0.1	0.51	0.35	1.05	0.24		0.51	0.35	0.43	0.31