

Special



Image for illustrative purpose only

Summary

[Request a quote](#)

[P series catalog](#)

[Industry Brochure Medical](#)

[Customer Drawing](#)

Number of contacts Low Voltage	14
Gender	Reverse Gender
Socket / Receptacle	Socket / Receptacle - Fixed Panel Rear Mounted
Locking system	Push-pull
Size	1P
Series	REDEL P - Push-Pull

https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/pkj-m1-4sl-dg.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Number of contacts Low Voltage	14
Contact Termination Low voltage	PCB - Straight
R (max) - electrical contact resistance	8.5 mOhm
Insert configuration value	1P.M14 - 14 Low Voltage
Footprint IPC Class3 compatibility	Yes
Class3 Productibility Level Compatibility	C (High Design Producibility - Reduced)
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated current	2 A
Test voltage contact-contact	0.85 (kV DC)
Contact retention	31 N
Air clearance	0.5 mm
Creepage distance	0.5 mm
Contact Dia.	0.5 mm (0.0197 in)
Gender	Reverse Gender

Form & Material

Shell style / Model id	PK - Fixed receptacle with two nuts (back panel mounting), straight print contacts
Socket / Receptacle	Fixed Panel Rear Mounted
Housing material	PEI (Polyetherimide), grey
Locking system	Push-pull
Keying	J: 2 keys (beta=205, Plug: female contacts, Receptacle: male contacts)
Colour	Grey
Variant	Grey front nut
Weight	4.97 g

https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/pkj-m1-4sl-dg.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Environment

Technical domain	Energy and Industrial, Medical, Test and Measurement, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	IP50
Endurance	> 5000 mating cycles
Temperature range	-50°C / +170°C
F ret (max)	150 N
F ret (min)	50 N
Steam sterilization	Compiles with ISO 17665:2024 sterilization standard for autoclave, ISO 11135:2014 for EtO, and ISO 11137-1, -2, -3 standards for gamma, e-beam x-ray. For more details on sterilization methods and cycles, please contact us.

Recommended By Lemo

Caps

Compatible cap	PBG.200.BMV
Cap 2	PBG.201.BMV

Tools

Spanner	POB.186.GN
Spanner 2	POP.125.GN

https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/pkj-m1-4sl-dg.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.