

Special



Image for illustrative purpose only

Summary

[Request a quote](#)

[M series](#)

[Application leaflet Security Defence](#)

Number of contacts Low Voltage	5
Wire Size/AWG	32 - 28
Gender	Standard
Socket / Receptacle	Socket / Receptacle - Free
Locking system	Ratchet
Jacket cable outside diameter [mm]	4.00 - 8.00 mm
Size	0M
Suggested matching part	FMN.0M.305.XLB
Series	M - Rugged Ratchet coupling

https://www.lemo.com/int_en/solutions/optima/m-ratchet-coupling/pm-n-0m-305-xlp.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

Number of contacts Low Voltage	5
Contact Termination Low voltage	Crimp
R (max)	6.1 mOhm
Insert configuration value	0M.305 - 5 Low Voltage
Insulator	L: PEEK
Rated current	6.5 A
Test voltage contact-contact	1.75 kV DC
Test voltage contact-shell	1.4 kV DC
Contact retention	22 N
Max. Conductor	0.09 mm ² (AWG 28)
Min. Conductor	0.035 mm ² (AWG 32)
Bucket Dia.	0.45 mm (0.018in)
Contact Dia.	0.7 mm (0.028in)
Wire Size/AWG	32 - 28
Gender	Standard

Form & Material

Shell style / Model id	PM - Free receptacle with knurled grip
Socket / Receptacle	Free
Housing material	Aluminium (nickel plated [SAE AMS QQ N 290], anthracite color) shell and nut, other pieces bronze/brass
Locking system	Ratchet
Keying	N: 3 keys (beta=165, gamma=30, plug: male contacts, receptacle: female contacts)
Colour	Grey
Weight	11.18 g

https://www.lemo.com/int_en/solutions/optima/m-ratchet-coupling/pmn-0m-305-xlp.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Environment

Technical domain	Motorsport, Security and Defence, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	IP68
Endurance	3000 mating cycles
Temperature range	-20°C / +200°C (max. temperature valid for short periods of use.)
EMI Shielding EIA 364-66A	>= 80 dB (1 GHz), >=70 dB (3 GHz), >= 58 dB (6 GHz), >= 40 dB (10 GHz)
Gunfire vibration	25 Hz - 2000 Hz, 3 axis (Apache helicopter)
Humidity (max)	21 days at 95%
Lighting strike EIA 364-76	10K amps - 6 times
Shock Resistance	300 g [3 ms]
Thermal shock	5 cycles: -65°C to +150°C
Vibration-Random	37.8 g rms - 3 axes, 4 hr amb [50 Hz - 2000 Hz]
Vibration-Sine	30 g, 3 axes, 12 hr [10 Hz - 2000 Hz]
Salt Spray Corrosion	max. 48 hr



Cable fixation

Cable termination protection	Heatshrink
Fixation type	Heatshrink
Jacket cable outside diameter [mm]	4.00 - 8.00 mm

Drawings

https://www.lemo.com/int_en/solutions/optima/m-ratchet-coupling/pmn-0m-305-xlp.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.



Dimensions

	A	B	C	D	Ls	Lr	P	X
mm.	13.1	8.8	12.7	8	25.6	25.6	5.3	6.7
in.	0.52	0.35	0.5	0.31	1.01	1.01	0.21	0.26

Recommended By Lemo

Contacts

Replacement contact [EGN.0M.656.ZZM](#)

Caps

Compatible cap [BMF.0M.200.XAZ](#)

Cap 2 [BMF.0M.200.XAZ](#)

Tools

Positionner [DCE.91.070.3MVM](#)

Extraction tool [DCC.07.04B.LAG](#)

Crimp tool [DPC.91.701.V](#)

https://www.lemo.com/int_en/solutions/optima/m-ratchet-coupling/pm-n-0m-305-xlp.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.