




FDI

ELI

TM

5.0" PCAP Touchscreen LCD Module for SBCs



ELI50-CPW

- **Cost-Effective Commercial Version**
- **5.0" LCD Panel with LED Backlight**
- **720 x 1280 (HD) with 1000:1 Contrast Ratio**
- **Projected Capacitive Touchscreen**
- **Optical Bonding for 70% Display Improvement**

Features

- PCAP Touchscreen with USB Device Interface
- Plug and Play interface to standard SBCs
- HDMI Input
- +12 Volt DC Input Power (typical)
- 300 nits Brightness (typical)
- 1000:1 Contrast Ratio (typical)
- EDID Support for Automatic Screen Configuration
- -20° to +70° C Operating Temperature Range
- Franchised Distribution Stocking
- Part Number: ELI50-CPW

Specifications

- Screen Size: 5.0 inches (vertical)
- Display Technology: a-Si SFT LCD
- Resolution: 720 x 1280 (HD)
- Brightness: 300 nits (typ)
- Contrast Ratio: 1000 : 1 (typ)
- Aspect Ratio: Wide 16x9
- Interface Input Mode: HDMI
- Colors: 16.7M (24 bit)
- Horizontal Viewing Angle: 85/85° L/R
- Vertical Viewing Angle: 85°/85° U/D
- Surface: 1.1 mm anti-fingerprint treated glass
- Reverse Scan: U/D, L/R
- Touchscreen: In-cell PCAP
- Touchscreen Interface: USB Device
- Touch Panel Hardness: 6H
- Touch Panel Force: 100gF (max)
- Active Area: 62.10 (W) x 110.40 (H) mm
- Response Time: 30ms (typ)
- Backlight: 12 LEDs
- Backlight Life: 30K hours (typ)
- Backlight Power Consumption: up to 61% of total
- Operating Temperature: -20° to 70° C
- Storage Temperature: -30° to 80° C
- Input Voltage: 7.5 - 24.0 VDC (±5% tolerance)
- Power Consumption: 150/250mA @ 12V (typ/max)
- RoHS Compliant: Yes
- Dimensions: 71.64 (W) x 145.4 (H) x 14.9 (D) mm
- Mounting: 3M 300LSE tape
- Weight: 94 grams (typ)

Compatible
With:



Available From:



www.teamfdi.com
(256) 883-1240



@TeamFDI
#TeamFDI



[YouTube.com/
FDIProducts](https://www.youtube.com/FDIProducts)

Rev 1.6 - 08/06/2025