







Customer Information Sheet

Specifications:  
Material:  
Housing = Glass-Filled PPS,  
UL94V-O, Black  
Contact = Phosphor Bronze  
Jackscrew = Stainless Steel  
Finish - Contacts (all over Nickel):  
22 = Gold on contact area,  
90/10 Tin/Lead on tails  
42 = Gold on contact area,  
100% Tin on tails  
05 = Gold  
Packing:  
Connector: Tube  
Screws: Bag  
For complete Specification, see  
Component Specification C005XX  
(Latest Issue)



| Table 1: Dimension Variants |         |         |         |
|-----------------------------|---------|---------|---------|
| Part No.                    | DIM 'A' | DIM 'B' | DIM 'C' |
| M80-54004XX                 | 2.00    | 9.00    | 14.0    |
| M80-54006XX                 | 4.00    | 11.00   | 16.0    |
| M80-54008XX                 | 6.00    | 13.00   | 18.0    |
| M80-54010XX                 | 8.00    | 15.00   | 20.0    |
| M80-54012XX                 | 10.00   | 17.00   | 22.0    |
| M80-54014XX                 | 12.00   | 19.00   | 24.0    |
| M80-54016XX                 | 14.00   | 21.00   | 26.0    |
| M80-54018XX                 | 16.00   | 23.00   | 28.0    |
| M80-54020XX                 | 18.00   | 25.00   | 30.0    |
| M80-54022XX                 | 20.00   | 27.00   | 32.0    |
| M80-54024XX                 | 22.00   | 29.00   | 34.0    |
| M80-54026XX                 | 24.00   | 31.00   | 36.0    |
| M80-54028XX                 | 26.00   | 33.00   | 38.0    |
| M80-54030XX                 | 28.00   | 35.00   | 40.0    |
| M80-54032XX                 | 30.00   | 37.00   | 42.0    |
| M80-54034XX                 | 32.00   | 39.00   | 44.0    |
| M80-54036XX                 | 34.00   | 41.00   | 46.0    |
| M80-54038XX                 | 36.00   | 43.00   | 48.0    |
| M80-54040XX                 | 38.00   | 45.00   | 50.0    |
| M80-54042XX                 | 40.00   | 47.00   | 52.0    |
| M80-54044XX                 | 42.00   | 49.00   | 54.0    |
| M80-54046XX                 | 44.00   | 51.00   | 56.0    |
| M80-54048XX                 | 46.00   | 53.00   | 58.0    |
| M80-54050XX                 | 48.00   | 55.00   | 60.0    |

Order Code: **M80-540XXXX**  
Total No. of contacts: \_\_\_\_\_  
04 to 50  
(Even numbers only)  
Finish: \_\_\_\_\_  
22 - Selective Gold + Tin/Lead  
42 - Selective Gold + 100% Tin  
05 - 0.75µm Gold All Over

|          |      |          |       |
|----------|------|----------|-------|
| JW       | 7    | 05.12.25 | 37127 |
| Initials | Rev. | Date     | CO    |
| JMB      | D    | 24.08.06 | 9393  |

Notes:  
1. Board mount screws supplied loose in a bag, not as shown.  
2. Additional screws available, order separately using P/N M80-2260000B

**HARWIN**  
www.harwin.com

This drawing and any information or descriptive matter set out hereon are confidential and copyright property of the Harwin group and must not be disclosed, loaned, copied or used for manufacturing, tendering or for any other purpose without their written permission.

TOLERANCES  
X. = ±0.50mm  
X.X = ±0.30mm  
X.XX = ±0.10mm  
X.XXX = ±0.01mm  
Angles = ±5°  
Unless stated

Third angle projection  
  
Sheet scale: 6:1  
Do not scale  
Sheet size: A3

MATERIAL:  
  
See above  
  
FINISH:  
  
See above

Title:  
  
Datamate J-Tek Male Right Angle Board  
  
Drawing number:  
  
**M80-540XXXX**  
SHT 2 OF 2