


[Click here for the 3D model.](#)

General Information

Series	A780
Dielectric	Hybrid Polymer
Style	SMD Can
Description	Surface Mount, Hybrid Aluminum Polymer
RoHS	Yes
Lead	V-Chip
Qualifications	AEC-Q200
AEC-Q200	Yes
Halogen Free	Yes
Shelf Life	52 Weeks
MSL	1

Dimensions

D	6.3mm +/-0.5mm	Capacitance	47 uF
L	5.7mm +/-0.3mm	Tolerance	20%
W	6.6mm +/-0.2mm	Voltage DC	35 VDC, 40.25 VDC (Surge)
H	6.6mm +/-0.2mm	Temperature Range	-55/+125°C
C	7.3mm +/-0.2mm	Rated Temperature	125°C
P	2mm NOM	Life	4000 Hrs
R	0.5 - 0.8mm	Dissipation Factor	12% 120Hz 20C
		ESR	70 mOhms (100kHz 20C)
		Ripple Current	880 mAmps (100kHz 125C)
		High Temperature Solder	Yes
		Leakage Current	16.45 uA (2min 20°C)

Packaging Specifications

Packaging	T&R, 380mm
Packaging Quantity	1000

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.