



Click [here](#) for the 3D model.

General Information

Series	EDH
Dielectric	Aluminum Electrolytic
Style	SMD Can
Description	Surface Mount, Aluminum Electrolytic
RoHS	Yes
Lead	V-Chip
AEC-Q200	No

Dimensions

D	16mm +/-0.5mm	Capacitance	22 uF
L	16.5mm +/-1mm	Tolerance	20%
W	2mm +/-0.2mm	Voltage DC	450 VDC, 500 VDC (Surge)
F	0.3mm MAX	Temperature Range	-25/+105°C
A	17mm +/-0.2mm	Rated Temperature	105°C
B	17mm +/-0.2mm	Life	2000 Hrs
C	18.7mm MAX	Dissipation Factor	25% 120Hz 20C
E	5.8mm +/-0.2mm	Ripple Current	85 mAmps (120Hz 105C)
G	1mm +/-0.2mm	Compare Ripple Current at 120Hz	0.085
P	6mm +/-0.2mm	High Temperature Solder	Yes
		Leakage Current	496 uA (2min 20°C)
		Impedance Ratio at -25C	4

Packaging Specifications

Packaging	T&R
-----------	-----

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.