


**TERMINAL END VIEW**

**PCB LAYOUT**

[Click here for the 3D model.](#)
**General Information**

|                          |                                                                                                                                                                                      |
|--------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Series                   | ALA7D                                                                                                                                                                                |
| Dielectric               | Aluminum Electrolytic                                                                                                                                                                |
| Description              | Snap-In, Aluminum Electrolytic                                                                                                                                                       |
| RoHS                     | Yes                                                                                                                                                                                  |
| Lead                     | 2 Pin                                                                                                                                                                                |
| Qualifications           | AEC-Q200                                                                                                                                                                             |
| Halogen Free             | Yes                                                                                                                                                                                  |
| Typical Component Weight | 95 g                                                                                                                                                                                 |
| Miscellaneous            | Vibration: <= 35mm 1.5mm displacement amplitude or 20G maximum acceleration. Vibration applied for three directions of 4-hour sessions at 10-2,000 Hz. (Capacitor clamped by body.). |
| Shelf Life               | 156 Weeks                                                                                                                                                                            |

**Dimensions**

|    |               |
|----|---------------|
| D  | 40mm +1mm     |
| L  | 45mm +/-2mm   |
| S  | 10mm +/-0.1mm |
| LL | 6.3mm +/-1mm  |
| F  | 2mm +/-0.1mm  |

**Packaging Specifications**

|                    |      |
|--------------------|------|
| Packaging          | Tray |
| Packaging Quantity | 36   |

**Specifications**

|                   |                                                                                       |
|-------------------|---------------------------------------------------------------------------------------|
| Capacitance       | 330 uF                                                                                |
| Tolerance         | 20%                                                                                   |
| Voltage DC        | 600 VDC, 660 VDC (Surge)                                                              |
| Temperature Range | -40/+85°C                                                                             |
| Rated Temperature | 85°C                                                                                  |
| Life              | 18000 Hrs (Rated Voltage And Ripple Current At 85C), 29000 Hrs (Rated Voltage At 85C) |
| ESR               | 399 mOhms (100Hz 20C), 277 mOhms (10kHz 20C)                                          |
| Ripple Current    | 2.685 Amps (100Hz 85C), 5.438 Amps (10kHz 85C)                                        |
| Leakage Current   | 1188 uA (5min 20°C)                                                                   |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.