




Click [here](#) for the 3D model.

General Information

Series	ELH
Dielectric	Aluminum Electrolytic
Description	Snap-In, Aluminum Electrolytic
RoHS	Yes
Lead	2 Pin
AEC-Q200	No

Specifications

Capacitance	3,300 uF
Tolerance	20%
Voltage DC	50 VDC, 63 VDC (Surge)
Temperature Range	-40/+85°C
Rated Temperature	85°C
Life	2000 Hrs
Dissipation Factor	30% 120Hz 20C
ESR	0.1206 Ohms (120Hz 20C)
Ripple Current	2.35 Amps (120Hz 85C)
Leakage Current	3 mA (5min 20°C)

Dimensions

D	22mm +1mm
L	30mm +2mm
S	10mm +/-0.5mm
LL	5.8mm +/-1mm
F	2mm +/-0.1mm

Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	400