


Click [here](#) for the 3D model.

General Information

Series	PHE426/F426
Dielectric	Metallized Polypropylene
Style	Radial
Features	Pulse
RoHS	Yes
Termination	Tinned Wire
Lead	Wire Leads
AEC-Q200	No
Typical Component Weight	0.337 g
Notes	Series Replaced by R75.

Dimensions

L	7.2mm MAX	Capacitance	0.047 uF
H	8mm MAX	Tolerance	5%
T	3.5mm MAX	Voltage DC	100 VDC, 74 VDC (105C)
S	5mm +0.6/-0.1mm	Voltage AC	63 VAC
H0	17mm NOM	Temperature Range	-55/+105°C
F	0.5mm NOM	Rated Temperature	85°C
		Dissipation Factor	0.05% 1kHz, 0.25% 100kHz
		Insulation Resistance	100 GOhms
		Max dV/dt	100 V/us
		Inductance	6 nH

Packaging Specifications

Packaging	T&R	Capacitance	0.047 uF
Packaging Quantity	2000	Tolerance	5%

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.