




Click [here](#) for the 3D model.

## General Information

|                          |                              |
|--------------------------|------------------------------|
| Series                   | R47 X2 440 VAC               |
| Dielectric               | Metallized Polypropylene     |
| Style                    | Radial                       |
| Features                 | Automotive Grade, EMI Safety |
| RoHS                     | Yes                          |
| Termination              | Cut (Tinned Wire)            |
| Lead                     | Cut                          |
| Safety Class             | X2                           |
| Qualifications           | AEC-Q200, ENEC, UL, cUL      |
| AEC-Q200                 | Yes                          |
| THB Performance          | No                           |
| Typical Component Weight | 9.573 g                      |

## Dimensions

|    |                    |
|----|--------------------|
| L  | 26.5mm +0.3/-0.5mm |
| H  | 22mm +0.1/-0.5mm   |
| T  | 13mm +0.2/-0.5mm   |
| S  | 22.5mm +/-0.4mm    |
| LL | 4mm +2mm           |
| F  | 0.8mm +/-0.05mm    |

## Packaging Specifications

|                    |           |
|--------------------|-----------|
| Packaging          | Bulk, Bag |
| Packaging Quantity | 300       |

## Specifications

|                       |              |
|-----------------------|--------------|
| Capacitance           | 0.33 uF      |
| Tolerance             | 10%          |
| Voltage DC            | 1000 VDC     |
| Voltage AC            | 440 VAC (X2) |
| Temperature Range     | -40/+110°C   |
| Rated Temperature     | 110°C        |
| Dissipation Factor    | 0.3% 1kHz    |
| Insulation Resistance | 100 GOhms    |
| Max dV/dt             | 300 V/us     |