


[Click here for the 3D model.](#)

General Information

Series	T543 HRA
Dielectric	Polymer Tantalum
Style	SMD Chip
Description	SMD, Polymer, Molded, Up Screening
Features	Non-Combustible, Low ESR, High Reliability
RoHS	No
Prop 65	WARNING: Cancer and reproductive harm - https://www.p65warnings.ca.gov/
SCIP Number	b064b03e-bd75-42af-b342-1fe94dec2340
Termination	Tin Lead (SnPb)
AEC-Q200	No
Typical Component Weight	98.3 mg
Shelf Life	52 Weeks
MSL	3

Dimensions

L	3.5mm +/-0.2mm	Capacitance	100 uF
W	2.8mm +/-0.2mm	Tolerance	10%
H	1.9mm +/-0.2mm	Voltage DC	6.3 VDC (105C)
T	0.13mm REF	Temperature Range	-55/+105°C
S	0.8mm +/-0.3mm	Rated Temperature	105°C
F	2.2mm +/-0.1mm	Humidity	60C, 90% RH, 500 Hours
A	1.9mm MIN	Dissipation Factor	8% 120Hz 25C
B	0.4mm +/-0.15mm	Failure Rate	N/A
E	2.2mm REF	ESR	25 mOhms (100kHz)
G	1.8mm REF	Ripple Current	2254 mA (rms, 100kHz 45C)
P	0.5mm REF	Leakage Current	63 uA (5min 25°C)
R	1mm REF	Testing and Reliability	10 Cycles Surge Current Testing At -55C +/-5C And +85C +/-5C
X	0.1mm +/-0.1mm REF		

Packaging Specifications

Packaging	T&R, 178mm
Packaging Quantity	2000

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.